


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	CHANGED PVC BODY MOLDING (ECN# 1263)	12/9/02	T CLARK
C	CORRECTED WIDTH DIMENSION OF D-SUB HOOD (ECN# 1451)	8/6/03	T CLARK
D	ECN1641: ADDED COMPONENT SPECIFICATION TABLE	1/15/04	DFP
E	ECN# 2831 ADDED UL94V-0 RATED TO INSULATOR MATERIAL	04/26/07	C.BERUBE

"P1"




MALE DVI-A
CONNECTOR

1.69



"J1"



FEMALE 15-PIN
HIGH DENSITY
D-SUB CONNECTOR

WIRING TABLE

"P1"	"J1"
C5	6, 7, 8
C4	13
C3	3
C2	2
C1	1
15	5, 10
14, 16	9
8	14
7	12
6	15
SHELL	SHELL

Component Specifications		
Material		
Housing	PVC	Color: Gray
Connector Shell	SPCC	
Connector Insulator	THERMOPLASTIC UL94V-0	
Connector Contact	Brass	
Hardware	Brass or Steel	
Internal Shielding	Copper foil	
Finish		
Connector Shell	Tin over Nickel	
Contact	Gold	
Electrical		
Current Rating	1.5 A	
Voltage rating	40 VDC, 500Vac (rms)	
Insulation Resistance	1000MΩ	
Contact Resistance	20mΩ max	
Environmental		
Operating Temperature range	-20°C to 85°C	

CS-211

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
.X ±.1
.XX ±.05
.XXX ±.005
CABLE LENGTH TOLERANCE
<300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY T CLARK	4/6/2002
CHECKED BY D PARHAM	4/12/2002
APPROVED BY C MCCORMICK	4/12/2002

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

L-com
CONNECTIVITY
PRODUCTS

45 BEECHWOOD DRIVE
NORTH ANDOVER, MA
01845

PRODUCT DESCRIPTION

DVI-A ADAPTOR

DRAWING TITLE

OUTLINE DRAWING

SIZE A	FSCM NO. 43321	DWG. NO. DMB601MF-OD1	REV. E
SCALE: NONE CAD FILE: DMB601MF-OD1.SLDDRW SHEET 1 OF 1			