

General ordering data

Order No.	0306120000
Part designation	SAKS 1/32 G20 GL 230VAC
Version	Fuse terminal, 10 mm ² , Screw connection, KrG, Medium yellow, TS 32
EAN	4008190038311
Qty.	10 pc(s).

Product notes

Note, technical data	Connections for 10-mm ² stranded conductors require a tightening torque of 2 Nm.
----------------------	--

Additional technical data

Colour of insulating material	Medium yellow
Connection direction	on side
End plate required	Yes
Installation advice	TS 32
Insulating material	KrG
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 60 °C, + 130 °C
Product family	SAK Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	5VA
Version	Fuse terminal

CSA rating data

Min. cross-section (CSA)	AWG 26
Max. cross-section (CSA)	AWG 10

Conductors for clamping (rated connection)

Clamping range, min.	0.5 mm ²
Clamping range, max.	16 mm ²
Type of connection	Screw connection
2nd type of connection	screwed
Connection direction	on side
No. of connections	2
Stripping length	12 mm
Clamping screw	M 4
Blade size	1.0 x 5.5 mm
Tightening torque range	1.2...2.4 Nm
Torque level with DMS electric screwdriver	4
Gauge to IEC 60947-1	B6
Solid, min.	0.5 mm ²
Solid, max.	16 mm ²
Stranded, min.	1.5 mm ²
Stranded, max.	10 mm ²

Conductors for clamping (rated connection)

Flexible, min.	0.5 mm ²
Flexible, max.	10 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	10 mm ²
AWG conductor size, min.	AWG 20
AWG conductor size, max.	AWG 8
AWG conductor size, min.	0.52 mm ²
AWG conductor size, max.	8.37 mm ²

Dimensions

Width	13 mm
Height of lowest version	61 mm
Length	54 mm

Disconnect terminals

Torque level with DMS electric screwdriver	4
--	---

Display element

Current	50 A
Operating voltage for display, max.	230 V
Type of voltage for indicator	AC/DC

Fuse terminals

Cartridge fuse	G-Si. 5 x 20
Current	50 A
Display	Neon lamp
Fuse holder (cartridge holder)	Screwable
Operating voltage, max.	230 V
Type of voltage for indicator	AC/DC

Rating data

Rated cross-section	10 mm ²
Rated voltage	500 V
Rated impulse voltage	4 kV
Rated current	6.3 A
Current with max. conductor	10 A

UL rating data

Min. cross-section (UL)	AWG 22
Max. cross-section (UL)	AWG 8

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000899
ETIM 3.0	EC000899

Classifications

eClass 4.1	27-14-11-16
eClass 5.0	27-14-11-16
eClass 5.1	27-14-11-16

Similar products

Order No.	Part designation	Version
0385320000	SAKS 1/32 G20 GL 115VAC	Fuse terminal, 10 mm ² , Screw connection, KrG, Medium yellow, TS 32
0309320000	SAKS 1/32 G25 GL 230VAC	Fuse terminal, 10 mm ² , Screw connection, KrG, Medium yellow, TS 32
0191220000	SAKS 1/G20	Fuse terminal, 10 mm ² , Screw connection, KrG, Medium yellow, TS 32
0191120000	SAKS 1/G25	Fuse terminal, 10 mm ² , Screw connection, KrG, Medium yellow, TS 32
0206820000	SAKS 2	Fuse terminal, 10 mm ² , Screw connection, KrG, Medium yellow, TS 32
0297520000	SAKS 3 G/5X30 500V	Fuse terminal, 10 mm ² , Screw connection, KrG, Medium yellow, TS 32
0321320000	SAKS 4	Fuse terminal, 10 mm ² , Screw connection, KrG, Medium yellow, TS 32
0162220000	SAKS 4 USA	Fuse terminal, 10 mm ² , Screw connection, KrG, Medium yellow, TS 32
0531820000	SAKS 6/GZ 500AC	Fuse terminal, 10 mm ² , Screw connection, KrG, Medium yellow, TS 32