

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [45971-3115](#)
Status: **Active**
Overview: [SEARAY* Plugs, Receptacles and Copper Flex Assemblies](#)
Description: SEARAY* Receptacle, 300 Circuits, 5.00mm Unmated Height, 10 Rows, with Pegs, Solder Charge™ Lead-Free

Documents:

3D Model	Application Specification AS-45970-002 (PDF)
Drawing (PDF)	Application Specification AS-45970-990 (PDF)
Product Specification PS-45970-001 (PDF)	Test Summary TS-45970-001 (PDF)
Product Specification PS-45970-002 (PDF)	Test Summary TS-45970-002 (PDF)
Application Specification AS-45970-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Receptacles
Series	45971
Application	Board-to-Board, Signal
Electrical Model	Yes
Overview	SEARAY* Plugs, Receptacles and Copper Flex Assemblies
Product Name	SEARAY*
UPC	883906234751

Physical

Circuits (Loaded)	300
Circuits (maximum)	300
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.372/g
Number of Rows	10
Orientation	Vertical
PC Tail Length	2.18mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Pick and Place Cap



EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[45971Series](#)

Mates With
[45970 SEARAY* Plug](#)

Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	Surface Mount
Unmated Height	5.00mm

Electrical

Current - Maximum per Contact	2.7A
Grounding to PCB	No
Voltage - Maximum	240V AC

Solder Process Data

Duration at Max. Process Temperature (seconds)	3
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	AS-45970-001, AS-45970-002, AS-45970-990
Electrical Model Document	EE-45970-010
Product Specification	PS-45970-001, PS-45970-002
S-Parameter Model	SP-45970-010
Sales Drawing	SD-45971-001
Test Summary	TS-45970-001, TS-45970-002

*SEARAY is a trademark of Samtec, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[45971-3115](#)