

Cable Knives

The Jokari brand offers cable and wire stripping products which are ideal for specialist users.

The products have unique, patented designs for specific applications and are manufactured using the highest quality materials.

They are suitable for flat and round cables up to 50mm Ø.



10160/270/1 Cable knives

Item Number	Ø	No.
T10160	4 - 16mm 5/32 - 5/8"	16
T10270	8 - 28mm 5/16 - 1 1/8"	27
T10271	8 - 28mm 5/16 - 1 1/8"	217S

Easy to use, safe and fast for round and lengthwise cuts. The cutting depth can be adjusted by screw, and a spare blade is stored inside the handle.



10280 Cable knife

Item Number	Ø	No.
T10280	8 - 28mm 5/16 - 1 1/8"	28H

With double sided trimming knife blade, hook and straight. Spring loaded for ease of use.

Jokari products offer users precision performance with reduced risk of damage, nicked wires and cables, making the tools ideal for use in domestic and commercial applications where safety is paramount.



10283 Cable knife

Item Number	Ø	No.
T10283	8 - 28mm 5/16 - 1 1/8"	28HX

Similar to No.10280. Economy model.

19000 Spare blades for cable knives

Item Number	i
T19000	spare blades

Spare blades for all cable knives.

A top quality product manufactured in Germany to the toughest standards. Each knife supplied with spare blade stored in handle.



All Jokari products are manufactured using high-grade, wear-resistant polymide. This material gives the product a very long life, as well as being resistant to knocks and damage.

Auto Strippers



20030 Auto stripper Flat cable

Item Number	Ø / AWG mm²	Ø
T20030	wire stripping 0.75-6.0/18-10	12mm 15/32"

For flat cable e.g. NM-B 14/2 or Romex. To strip outer sheathing and inner insulation. No adjustment necessary.



20040 Auto stripper Single core super 4

Item Number	Ø / AWG mm²	No.
T20040	0.5-4.0/20-11	4

For solid and stranded conductors. Ergonomic wire stripper with integrated safety cutter for wires up to 2.0mm / 5/64" Ø. No adjustment necessary.

'Pliers' style automatic wire strippers manufactured in Germany to exacting standards. The most efficient method of stripping the insulation from wire.



20060 Auto stripper
Special

Item Number	Ø / AWG mm²	Ø
T20060	wire stripper 0.5-6.0/20-10	2.8mm

Ergonomic Wire Stripper for quick and precise no-nick stripping. Automatic adjustment for a wide range of wire diameters from 0.5 - 6.0 mm² (AWG 20 - 10). Easy handling due to side insertion of wire. Adjustable wire stop for equal stripping length. Integrated wire cutter for max. 2.8 mm Ø.



20090 Auto stripper

Item Number	Ø / AWG mm²	No.
T20090	6-12/10-15	6-16

For conductors with large cross sections. Also suitable for stripping sheathing from 3 x 0.75mm Ø PVC flex. No adjustment necessary.



20450 Auto stripper
High strip

Item Number	Ø / AWG mm²
T20450	0.5-4.0/20-11

Ergonomic precision wire stripper for conductors with hard to strip insulations such as rubber, silicone, TPE etc. With 5 - 15mm adjustable length stop.

Order Online
www.carlkammerling.com



Cable / Wire Strippers



30010 Coax cable stripper

Item Number	Ø
T30010	Cable stripping 4.8-7.5mm / 3/16 - 9/32"

For all standard COAX cables e.g. TV coax, RG58U, RG59U etc. Also for 3 x 0.75mm² PVC flex. Stripping of outer sheathing with one side of tool and inner insulation with the other side. No adjustment necessary. With length stop.



30120 Cable stripper

Item Number	Ø	No.
T30120	Cable stripping 8-13mm / 5/16 - 1/2"	12

For round cable. Can be used on cable from 8mm to 13mm without the need for adjustment.



30140 Cable stripper
Twin & earth flat

Item Number	Ø / AWG mm²	Ø
T30140	Conductor stripping 0.8, 1.5, 2.5/20, 16, 14	12mm 1/2"

For flat or oval cables up to 12mm/1/2" wide. With additional precision conductor stripping blades.



30150 Cable stripper
FP

Item Number	Ø / AWG mm²	Ø
T30150	Conductor stripping 0.2, 0.3, 0.8, 1.5, 2.5, 4.0 / 24, 22, 20, 16, 14, 12	8-13mm 5/16 - 1/2"

For fireproof cable. Retractable safety trimming knife blade and pocket clip. For standard and solid conductors. With additional precision conductor stripping blades.



30160 Data Comm stripper
PC

Item Number	Ø / AWG mm²	Ø
T30160	Conductor stripping 0.2, 0.3, 0.8, 1.5, 2.5, 4.0 / 24, 22, 20, 16, 14, 12	5-15mm 3/16 - 5/8"

For PVC insulated data communication, conductor cables e.g. IBM type 1 and type 2 etc, stranded and solid conductor. With additional precision conductor stripping blades.

Our customers are
currently enjoying:

- Same day despatch
- 98% stock availability
- 24 hour online ordering

