


500688 – USB Standard “Type A” USB Plug to 4 Pin Single Row Housing

This cable is required for a USB interface with Bergquist controllers 500697 or 500698



PIN ASSIGNMENT			
CON 1		CON 2	
1	RED (#24)	1	
2	WHITE (#28)	2	△
3	GREEN (#28)	3	△
4	BLACK (#24)	4	
SHELL			

NOTE: (說明):

1. LENGTH OF CABLE-CUTTING: 1550±10mm;
(1. CABLE 裁線長度: 1550±10mm.)
2. THE LENGTH OF JACKET STRIPPIN OF CON1: 13±2mm;
THE LENGTH OF JACKET STRIPPIN OF CON2: 25±2mm;
(2. CABLE CON1端剝外被長度: 13±2mm;CON2端剝外被長度: 25±2mm.)
3. 100% INSULATIONSHORTMISS-WIRE TEST;
(3. 100% 絕緣、短路、反線測試.)
4. TEST CONDITON: CT≤2Ω IS≥5MΩ.
(4. 測試條件:CT≤2Ω IS≥5MΩ.)

F	TERMINAL	200PH-T (A2001-TP or EQUAL)	4PCS
E	HOUSING	200PH-04P (A2001H-4P or EQUAL)	1PCS
D	外模	PVC-45P 貝吉色	6.0g
C	CONN	USB A TYPE 公頭 白色膠芯 端子鍍一般金	1SET
B	H.S.TUBE	OD*L=5.0*10mm BLACK	1PCS
A	CABLE	UL 2725 #24*2C+#28*1P+AEB 貝吉色 L=1550mm	1PCS
NO	NAME	SPECIFICATION	QTY