

SECURITY CHAINS, ACCESSORIES, PADLOCKS & CABLE LOCKS

SECURITY CHAINS & ACCESSORIES

PRODUCT	X-SECTION	SIZES(MM)	GRADE	SLEEVEING
Welded Steel, Case Hardened chains				
HARDLINK		6,8	Standard	Plastic•Fabric
QUADLINK		8,10	Medium	Plastic•Fabric
STRONGLINK		4,5,6,8,10	Medium	Thermoplastic
HEXLINK		12	High	Fabric
Alloy Steel, Through Hardened and Tested chains				
SUPERQUAD ★		6,8,10,14	High	Thermoplastic
SUPERHEX ★●		10,13	High	Thermoplastic
SUPERLINK ★●		10,13,16	Highest	Plastic•Fabric
★ Sold Secure Approved ● Thatcham Approved				

ACCESSORIES

Combined with our top security chains, these provide strong anchorage points to the ground.



Ground Anchor ★●



Earthscrew
Ground Anchor

PADLOCKS

Produced to our own specification and to ISO 9000 standards, the EC Security padlock range has been combined with a selection of tested proprietary padlocks to offer a range of quality security options. Our "Extra Heavy-Duty" locks are "Sold Secure" and "Thatcham" approved matching our higher grade security chains.

STANDARD SECURITY



Brass Padlock



Resettable
Combination
Padlock

MEDIUM SECURITY



Discus Padlock



Laminated Steel
Padlock



Close Shackle
Padlock

HEAVY-DUTY



Shutter Lock



Chain Lock



Armoured Block
Lock

EXTRA HEAVY-DUTY



Armoured Double
Slot
Lock



Solid Hardened
Block Lock ●



Solid Hardened
Padlock ★●

CABLES & CABLE LOCKS

Ideal for solving many outdoor and domestic security problems. Used with cycles, motorbikes, trailers, caravans, garden equipment, power tools and boats.



Spiral Cable
Locks



Steel Security
Cables



U-Shackle
Locks



Steel
Locking
Cable



Combination
Cable Locks



Steel Cable &
Shackle Locks



Hi-Grade
U-Shackle
Locks



Heavy Duty
Steel Locking
Cable



Heavy Duty
Spiral Cable
Locks



Heavy Duty
U-Shackle
Locks



Steel Joint
Lock

WELDED STEEL CASE HARDENED CHAINS

Hardlink

Standard Level

Chain link cross section



Good, basic security chain. Case hardened, 6 & 8mm thick welded steel chain. Zinc plated for corrosion resistance. With plastic sleeve.

Product Code	Chain Size (mm)	Length (cm)
923 50	6	60
923 51	6	90
923 52	6	120
923 55	8	90
923 58	8	120
923 61	8	150

Stronglink

Medium Level

Chain link cross section

A very popular, high quality, general purpose security chain range. Welded steel chain 4-10mm thick with deep case hardening for hacksaw resistance. Zinc plated and protected by red thermo-shrunk sleeving.



6, 8 & 10mm also available unsleeved in lengths up to 10metres

Product Code	Chain Size (mm)	Length (cm)
483 21	4	60
483 22	4	80
483 31	5	60
483 32	5	80
483 40	6	60
483 43	6	90
483 46	6	120
483 73	8	90
483 76	8	120
483 77	8	150
483 84	10	90
483 86	10	120
483 87	10	150
483 89	10	200

Quadlink

Medium Level

Chain link cross section



Square section, steel chain. 10mm thick, case hardened and zinc plated in plastic or fabric sleeve. For heavier duty applications.

Product Plastic	Code Fabric	Chain Size (mm)	Length (cm)
923 80	923 71	10	90
923 82	923 72	10	120
923 84	923 73	10	150
923 86	923 74	10	200

Hexlink

Heavy Duty

Chain link cross section



12mm thick hexagonal section links for heavy duty applications. Case hardened for high resistance to hacksaws. Zinc plated for corrosion resistance. High security rating. With heavy duty flexible fabric cover to protect paintwork.

Product	Dimensions Ø(mm) x L(cm)
95380HC	12 x 150
95382HC	12 x 200

Hi-Grade Alloy Steel Chains Through Hardened & Case Hardened

Superquad

Heavy Duty

Chain link cross section



High grade, square section chain made from special alloy steels for maximum strength. Through- and case hardened for high resistance to hacksaws and boltcutters. Bright zinc plated with blue thermoshrunk sleeve. 14mm chain in plastic or fabric sleeve. **High security rating.**



10mm & 14mm also available
unsleeved in lengths up
to 10metres

Product Code	Chain Size (mm)	Length (cm)
493 41	6	60
493 43	6	90
493 46	6	120
493 73	8	90
493 76	8	120
493 77	8	150
493 83	10	90
493 86	10	120
493 87	10	150
493 89	10	200
493 91	14	120
493 92	14	150
493 94	14	200

Superlink

Extra Heavy Duty

Chain link cross section



Our heaviest duty chain made from highest grade alloy steels with a three stage through- and case hardening to give maximum possible resistance to saws and boltcutters. Plated in a distinctive gold colour and covered in a thick plastic sleeve or flexible fabric cover. **Highest security rating.**




Also available unsleeved in
lengths up to 10metres

Product Code	Chain Size (mm)	Length (cm)
903 43	10	90
903 46	10	120
903 47	10	150
903 49	10	200
903 76	13	120
903 77	13	150
903 79	13	200
903 86	16	120
903 87	16	150
903 89	16	200

ACCESSORIES

Earthcrew Ground Anchor

Medium Level



Unique design screws into the ground to provide a very strong anchorage point. Galvanised steel. Quick and simple to use. Ideal for numerous DIY and gardening tasks or for tethering animals.

Product Code	Dimensions Ø x L x W (mm)
523 30GC	12 x 566 x 86

Trojan Ground Anchor

Extra Heavy Duty



Thick case hardened steel with unique double bridge design. Floor fitting using four fixing bolts with steel ball inserts. Takes up to 13mm chain. Easy to fit with full instructions included. Red epoxy coated finish.

Product Code	Dimensions Ø x L x W (mm)
523 87RC	68 x 150 x 150

Superhex

Extra Heavy Duty

Chain link cross section



High tensile, alloy steel chain with hexagonal section for very high rating at lower weight. Core- and case hardened for maximum cutting resistance. Bright zinco-chrome plating. With plastic or fabric sleeving. **Very high security rating.**



Product Code	Chain Size (mm)	Length (cm)
953 16	10	90
953 17	10	120
953 18	10	150
953 19	10	200
953 40	13	120
953 42	13	150
953 44	13	200

Also available unsleeved in lengths
up to 10metres



Brass Padlock

Standard Level



- Universally popular range
- Solid brass body
- Hardened steel shackle
- 3 keys

Iron padlocks also available in most sizes.

Sizes: 20, 25, 32, 38, 50, 63mm

Long shackle versions: 38, 50mm

Solid Steel Padlock

Heavy Duty



- Extra thick steel body
- Hardened, sprung shackle
- Anti-drill plate
- Double ball locking
- Satin nickel plated

Sizes: 50, 65mm

Long shackle versions: 50, 65mm

Discus Padlock

Medium Level



- Stainless steel body
- Hardened steel shackle
- 5 pin cylinder

Sizes: 60, 70, 90mm

Brass Block Lock

Heavy Duty



- Extra thick solid brass body
- Hardened, 11mm steel shackle
- Special high security cylinder
- Satin nickel plated

Sizes: 70, 80mm

Close Shackle Padlock

Medium Level



- Solid brass body
- Hardened, steel shackle
- Special high security cylinder
- 4 reversible keys
- Satin nickel finish

Sizes: 50, 60, 70mm

Stainless Steel Armoured Lock

Heavy Duty



- Stainless steel armoured casing for protection
- 12mm hardened steel shackle
- 6-pin security cylinder
- Takes up to 14mm chain

Sizes: 60, 80, 90mm

Brass Shutter Lock

Medium Level



- Thick brass body
- Hardened steel shackle
- Sprung shackle operation

Sizes: 60, 70, 80mm

EC Series 10

Combination Lock

Standard Level



Ideal for use on luggage, bags, lockers or any light security application where keyless locking is preferred. The dial combinations are easily and quickly reset as many times and as often as needed.

- Solid brass body
- Chrome plated steel shackle
- 3/4 digit code system
- Resettable combination

Product		Body (mm)		Shackle (mm)		
Code	Size	Width	Height	Diam	Inside Width	Height
P0102	20mm	20	31	3	9	21
P0103	30mm	30	36	4	13	24

EC Series 50

Laminated Steel Padlock

Medium Level



The steel laminations make this a very strong lock body. With a high quality dual locking mechanism, anti-pick pins and hardened steel shackle, this is one of the best laminated steel locks available. A durable vinyl bumper protects the surface of items to be locked.

- Precision steel laminated construction
- Hardened steel shackle - open sprung
- Double locking
- 4/5-pin cylinder mechanism
- Vinyl bumper guard
- Long shackle versions available

Product		Body (mm)		Shackle (mm)		
Code	Size	Width	Height	Diam	Inside Width	Height
P0503	30mm	30	26	5	14	17
P0504	40mm	40	34	6	20	22
P0505	50mm	50	39	9	23	29
P0507	65mm	65	48	10	30	35
P050W	LS40/50	40	34	6	20	51
P050X	LS50/50	50	39	9	23	51

EC Series 100

Armoured Chainlock

Heavy Duty



Unique, compact design specially for use with high quality security chains. The thick hardened steel casing gives resistance to hacksaws, boltcutters and levers. With high quality security chains these locks are very popular for heavy duty applications such as motorcycles, agricultural and plant hire equipment security.

- Hardened steel casing
- Hardened steel shackles
- Anti-pull shackle heads
- 6/7 pin cylinder mechanism
- Anti-drill guard

	Product	5-7 mm	8-10 mm
Code		U1005	U1008
Body	Width	55	60
	Height	35	45
	Thickness	35	38
Shackle	Diam	7	9.5

EC Series 120 Armoured Double Slot Lock

Extra Heavy Duty



Combining the strength and high security levels of an armour plated, double-slot lock with a PVC coating to protect lock and paintwork. With steel ball locking and a rotating anti-drill guard over the cylinder. A unique and practical design for use with high quality security chains and locking bars. Ideal for vans, boats, motorcycles, trailers.

- Hardened steel casing & shackle
- PVC coated body
- Anti-pull shackle head
- Quality 5-pin cylinder
- Anti-drill guard

	Product	90 mm
Code		A1208
Body	Width	80
	Height	57
	Thickness	30
Shackle	Diam	10
	Width	11.5
	Height	10.5

EC Series 130 Solid Hardened Block Lock

Extra Heavy Duty



Machined from solid alloy steel, then hardened, this is one of the toughest locks available. A heavy nickel chrome plating provides corrosion resistance. Fitted with a special high security radial cylinder mechanism, this is a very high specification lock made to exacting standards.

- Hardened all over
- 12mm hardened steel shackle
- Special radial key cylinder
- Anti-drill guard
- Anti-pull shackle head

	Product	72 mm	87mm
Code		A1307	A1308
Body	Width	72	87
	Height	60	63
	Thickness	25	25
Shackle	Diam	12	12
	Width	30	36
	Height	14.5	16

EC Series 350 Solid Hardened Padlock

Extra Heavy Duty



One of the toughest locks available internationally - made by ABLOY. With a solid alloy steel hardened body, extra thick 14mm hardened boron-alloy shackle and unique rotating disc cylinder system. Specially designed for use in severe conditions. Gives highest protection against drilling, sawing, cutting, twisting and shimming.

- Solid, hardened alloy steel body
- 14mm hardened boron alloy shackle
- Unique 11 disc cylinder system
- Over 2 million key combinations
- High corrosion resistance

	Product	72 mm
Code		U350
Body	Width	72
	Height	58
	Thickness	30
Shackle	Diam	14
	Width	31
	Height	25

EC211 - Spiral Cable Lock



- Popular design easy to use
- Thick braided steel cable for cutting resistance
- Self-coiling with easy-fit carry bracket

Product Code	Dimensions Ø x L(mm)
SECC110	8 x 1000
SECC111	10 x 1000
SECC112	12 x 1000

EC214 - Steel Security Cables



- 1.8m length heavy duty cables with eyes
- Made from braided steel for greater flexibility
- With double loop design to maximise on length
- Combine with padlock for a good, multi-purpose security system

Product Code	Dimensions Ø(mm) x L(mm)
SECC141	10 x 1800
SECC142	12 x 1800
SECC143	15 x 1800

EC213 - Combination Cable Locks



- 4 digit combination lock
- Strong braided steel cable
- Self-coiling with mounting bracket

Product Code	Dimensions Ø x L(mm)
SECC131	10 x 1500
SECC132	12 x 1500

EC214A - Extra Long Steel Security Cables

Extra long heavy duty cables with double loops, as per EC214.

Length: 2 - 9metres

Product Code	Dimensions Ø(mm) x L(mm)
SECC144	12 x 2100
SECC145	12 x 4500
SECC146	12 x 9000

EC215 - Steel Cable & Shackle Locks



- Extra strong 15mm or 20mm steel braided cable
- 14mm steel shackle resists cutting and sawing
- Tubular cylinder mechanism for added security

- Ideal for securing to posts
- All vinyl coated with rotating dust cap on lock

Product Code	Dimensions Ø x L(mm)
SECC151	15 x 1500
SECC152	20 x 1500

EC212 - Heavy Duty Spiral Cable Locks



- Tubular cylinder lock with dust cap
- Heavy braided steel cable resists cutting
- Vinyl covered to protect paintwork
- Self-coiling with bracket

Product Code	Dimensions Ø x L(mm)
SECC121	10 x 1000
SECC122	12 x 1000

EC216 - U-Shackle Lock



- Popular, effective design
- 14mm hardened steel shackle resists cutting
- Tubular cylinder lock with dust cap
- Vinyl coated to protect paintwork
- With easy-fit carrying bracket

Product Code	Dimensions Ø x W x L(mm)
SECC161	14 x 180 x 245
SECC162	14 x 180 x 320

EC218 - Steel Locking Cable



- Strong 15mm braided steel in durable vinyl sleeve
- Flexible for easy use
- Integrated 7-pin tubular locking mechanism
- Weather resistant

Product Code	Dimensions Ø x L(mm)
SECC181	15 x 1000

EC221 - Hi-Grade U-Shackle Lock



- 14mm hardened steel shackle for cutting resistance
- Hi grade lock system with fitted dust cover
- Double locking with key retention
- Vinyl covered for paintwork protection
- With quick-fit carrying bracket

Product Code	Dimensions Ø x W x L(mm)
SECC165	14 x 166 x 245

EC219 - Heavy Steel Locking Cable



- An impressive 25mm thick cable helps make this a real deterrent
- Made from heavy duty braided steel
- Also with vinyl coating to protect cable and paintwork
- Cable slots into integral locking mechanism

Product Code	Dimensions Ø x L(mm)
SECC191	25 x 1200

EC217- Heavy Duty U-Shackle Lock



- 18mm hardened steel shackle for extra strength
- Tubular cylinder lock with rotating dust cap for added protection
- Paintwork protected due to heavy vinyl coating
- Ideal for the quick and easy securing of bikes to posts
- With carrying bracket for easy access and storage

Product Code	Dimensions Ø x W x L(mm)
SECC171	18 x 170 x 320

EC220 - Steel Joint Lock



- 22mm thick hardened steel shell with strong inner cable
- Highly flexible for easy use and transportability
- Tubular cylinder lock with dust cap for protection
- Complete with radial keys

Product Code	Dimensions Ø x L(mm)
SECC201	22 x 1200