



Dimensions: In.

■ Specifications:

- Core type/size: EI-41
- Primary rated voltage & line frequency: 115V 60Hz
- Exciting current: 115V 60Hz, 65mA max.
- Secondary rating: with 5% tolerance
 - Lead number: 3-4-5
 - Rated voltage: AC 24.0VCT
 - Rated load: AC 200mA
 - Open voltage: 27.6VAC max.
 - Regulation: less than 15%
- Hi-pot test: apply 60Hz 1.5KV for 1 minute between the primary windings and the core, and between primary and secondary
- Insulation test: 500VDC 100MΩ min. between windings, and between primary and core

Lead Specifications:

- Color: 1-black, 2-black, 3-red, 4-white, 5-red
- Length: 153mm
- Stripped: 9mm
- Tinned: 9mm
- Description: 22AWG

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

41FK200