

TLSD-12-D-02.00-01-L-RN1

TLSD SERIES

COST EFFECTIVE IDC SOCKET CABLES

TYPE	NO. PINS PER ROW	END OPTION	LENGTH	01	PLATING OPTION	OTHER OPTION
	-05, -08, -10, -12, -13, -15, -17, -20, -22, -25 (Call for other sizes)		-"XX.XX" = Assembled Length		-L = 10μ" (0.25 μm) Gold on contact area	
	-S = Single End	-D = Double End				
				-N = Notch Polarization		-RW = Reverse Wiring Black wire opposite position #1.
				-SR = Strain Relief		-RN1 = Reverse Notch End 1 Reverse notch option on end 1 only. Not Available with -R option.
				-P "XX" = Position Polarization Specify "XX" as position number. Same position will be polarized on both ends.		-RN2 = Reverse Notch End 2 Reverse notch option on end 2 only. Not Available with -R option.
						-B "XX" = Breakout Specify "XX" as number of conductors to be broken out. Breakout starts with Number 1 lead indicated by brown wire or red stripe. Shown on top side.
						-D "XX" = Daisy Chain Double Row Connectors Outer Most (End of assembly)
				-R = Reversed	-M = Middle Reverse Requires -DXX	-O = Outside Reverse Requires -DXX

Due to technical progress, all designs, specifications and components are subject to change without notice

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 **SAMTEC NORTHERN CALIFORNIA** • Tel: 408-395-5900 **SAMTEC SOUTHERN CALIFORNIA** • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 **SAMTEC UNITED KINGDOM** • Tel: 44 1236 739292 **SAMTEC GERMANY** • Tel: 49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 **SAMTEC ITALY** • Tel: 39 039 6890337 **SAMTEC NORDIC/BALTIC** • Tel: +46-84477280 **SAMTEC BENELUX** • Tel: 44 1236 739292
SAMTEC ISRAEL • Tel: 972-3-7526060 **SAMTEC INDIA** • Tel: +91-80-3272 1612 **SAMTEC ASIA PACIFIC** • Tel: 65 6745-5955 **SAMTEC JAPAN** • Tel: 045-475-1385 **SAMTEC CHINA** • Tel: 86-21-6083 3766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 **SAMTEC HONG KONG** • Tel: 852-26904858 **SAMTEC KOREA** • Tel: 82-31-717-5685 **SAMTEC ANZ** • Tel: 613 9580 0683