



PLOT SCALE: .225/ DIMSCALE: .200

UNLESS OTHERWISE NOTED		
DIMENSIONS ARE IN INCHES	TOLERANCES ARE:	
ONE DECIMALS ± .1[.25]	THREE PLACE DECIMALS ± .005[.127]	ANGLES ± 2°
TWO DECIMALS ± .01[.25]	FOUR PLACE DECIMALS ± .0020[.051]	

TITLE:	.200 SOCKET POWER ASSEMBLY
--------	-------------------------------

DWG NO:
PSS-XX-XX-X-X-XX
SHEET 1 OF 2



PSS-XX-XX-X-X-XX

No. OF POSITIONS _____
-02 THRU -20

LEAD STYLE _____

-01: .090 TAIL (SEE FIG 1)
(USE C-124-XX-XX)

-02: SURFACE MOUNT (SEE FIG 2)
(USE C-124-XX-XX)

OPTION
 -K: POLYIMIDE
 FILM PAD (SEE
 SHEET TWO)
 -TR: TAPE & REEL
 (AVAILABLE ON -02
 LEAD STYLE, -02 THRU -14
 POSITIONS ONLY)

ROW SPECIFICATION
-S: SINGLE ROW
(USE PSS-20-200)

PLATING SPECIFICATION
 -T: TIN (USE C-124-XX-T)
 -TM: MATTE TIN (USE C-124-XX-T)
 -H: HEAVY GOLD (USE C-124-XX-H)

NOTES:




- NOTES:
1. MAX ALLOWABLE BOW: .005 IN/IN AFTER ASSEMBLY
 2. PUSHOUT FORCE SHALL BE: 2 lb MINIMUM.
 3. (C) REPRESENTS A CRITICAL DIMENSION.
 4. INSERTION FORCE: 1.75 LB AVG
 5. WITHDRAWAL FORCE: 1.25 LB AVG
 6. ENDWALL THICKNESS: .021

FIG 1

-01 LEAD STYLE

FIG 2

-02: SURFACE MOUNT
(SAME AS FIG 1 UNLESS OTHERWISE STATED)





INPROCESS FOR -02



No OF POS	COPLANARITY
02-14	.006
15-20	.008

PACKAGING VIEWS



LEAD STYLE	PACKAGING TUBE	PLUG
-01	PT-1-24-11-09	TP-09
-02	PT-1-24-04-15	TP-03

MATERIAL:
INSULATOR: VECTRA E130i
COLOR: BLACK
CONTACT: BeCu 174 HT

MAX FLASH ALLOWED: .020 [.51]

santec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: PURVIS 08-13-98

PSS-XX-XX-X-X-XX
SHEET 1 OF 2

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN PERMISSION OF SAMTEC INC.