



THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE (SQUARE WAVE)	3	V _{p-p}
OPERATING VOLTAGE RANGE	1 ~ 30	V _{p-p}
RATED CURRENT (MAX)	1	mA
CAPACITANCE	10,000±30%	pF
MINIMUM SPL @ 10 CM	78	dBA
RESONANT FREQUENCY	4,000±500	Hz
OPERATING TEMPERATURE	-20 ~ +70	°C
STORAGE TEMPERATURE	-30 ~ +80	°C
HOUSING MATERIAL	MPPO	—
TERMINAL MATERIAL	TIN-PLATED PHOSPHOR BRONZE	—
WEIGHT	1	grams



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME
AT-152.DWG

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	5/7/02	
A	REVISED TO NEW TEMPLATE	6/16/04	R. W.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.5 AND
ANGLES ARE ±3°.



projects®
unlimited

Dayton, Ohio

APPROVALS DATE

DRAWN *RABL* 5/02

APPROVED *S.J.* 6/02

DO NOT SCALE DRAWING

TRANSDUCER(PIEZO)
AT-152

SIZE
A

DRAWING NO.
AT-152

SCALE: N.T.S.

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AT-152](#)