


PVC INSULATED PIN TERMINALS



Specifications

- **Maximum Electrical Rating:** 600 Volts
- **Maximum Temperature:** +75°C
- **Terminal Material:** Copper
- **Plating:** Electro Tin Plated
- **Insulated Material:** Vinyl (PVC)



Ordering Information:

Wire Range AWG / mm ²	NTE Part Number	Dimensions inch(mm)					
		B	L	F	E	D	d1
22 – 18 AWG 0.5 – 1.5mm ²	76-IPT22	.075 (1.9)	.866 (22.5)	.492 (12.5)	.394 (10.0)	.161 (4.1)	.067 (1.7)
16 – 14 AWG 1.5–2.5mm ²	76-IPT16	.075 (1.9)	.866 (22.5)	.492 (12.5)	.394 (10.0)	.177 (4.5)	.091 (2.3)
12 – 10 AWG 4–6mm ²	76-IPT12	.110 (2.8)	1.031 (26.2)	.539 (13.7)	.492 (12.5)	.256 (6.5)	.134 (3.4)