



**Material:**

- Cable: USB1.1 E189529 UL2725 28#/1P+24#/2C+AEB
  - OD 4.7MM
  - Beige (IV-29#)
- P1 Connector: USB A Male Shell
  - Pin G/F
  - 4PCS Type
  - Insulator color: white
  - Shell Plate Nickel
- P2 Connector: USB A Male Shell
  - Pin G/F
  - 3PCS Type
  - Insulator color: white
  - Shell Plate Nickel
- Outer Jacket: Beige (IV-29#) PVC-40P
- 80°C 30V VW-1

PIN Assignment:



1PC / PE Bag

**Electrical:**

- 100% short, open, miswire test
- Conduct resistance: 2Ω Max.
- Insulation resistance: 5MΩ Min.
- Dielectric test: 300V DC



Scale	1:1						Name	Item No.
TOLERANCE						Drawn	01.04.12	<b>AK672-2-R</b>
X.X	±0.40					Approved		
X.XX	±0.25							Title
X.XXX	±0.15							USB 1.1 Cable - A Male <=> B Male, Beige, 2 Meters
Angle	±3°							Drawing No.
								Replace
								Sheet
		Modification	Date	Name				



	<b>rev00</b>