




Cable Length L		Part Number	Max. IL
Meters	[Inches]		
1m ± 0.05m	[39.37" ± 1.97"]	17-300330-01	0.20 dB
2m ± 0.05m	[78.74" ± 1.97"]	17-300330-02	0.20 dB
3m ± 0.05m	[118.11" ± 1.97"]	17-300330-03	0.20 dB
4m ± 0.08m	[157.48" ± 3.15"]	17-300330-04	0.20 dB
5m ± 0.08m	[196.85" ± 3.15"]	17-300330-05	0.20 dB
6m ± 0.08m	[236.22" ± 3.15"]	17-300330-06	0.20 dB
7m ± 0.08m	[275.59" ± 3.15"]	17-300330-07	0.20 dB
8m ± 0.15m	[314.96" ± 5.91"]	17-300330-08	0.20 dB
9m ± 0.15m	[354.33" ± 5.91"]	17-300330-09	0.20 dB
10m ± 0.15m	[393.70" ± 5.91"]	17-300330-10	0.21 dB
11m ± 0.15m	[433.07" ± 5.91"]	17-300330-11	0.21 dB
12m ± 0.15m	[472.44" ± 5.91"]	17-300330-12	0.21 dB
13m ± 0.15m	[511.81" ± 5.91"]	17-300330-13	0.21 dB
14m ± 0.15m	[551.18" ± 5.91"]	17-300330-14	0.21 dB
15m ± 0.15m	[590.55" ± 5.91"]	17-300330-15	0.21 dB
16m ± 0.30m	[629.92" ± 11.81"]	17-300330-16	0.21 dB
17m ± 0.30m	[669.29" ± 11.81"]	17-300330-17	0.21 dB
18m ± 0.30m	[708.66" ± 11.81"]	17-300330-18	0.21 dB
19m ± 0.30m	[748.03" ± 11.81"]	17-300330-19	0.21 dB
20m ± 0.30m	[787.40" ± 11.81"]	17-300330-20	0.21 dB

Cable Length L		Part Number	Max. IL
Meters	[Inches]		
21m ± 0.30m	[826.77" ± 11.81"]	17-300330-21	0.21 dB
22m ± 0.30m	[866.14" ± 11.81"]	17-300330-22	0.22 dB
23m ± 0.30m	[905.51" ± 11.81"]	17-300330-23	0.22 dB
24m ± 0.30m	[944.88" ± 11.81"]	17-300330-24	0.22 dB
25m ± 0.30m	[984.25" ± 11.81"]	17-300330-25	0.22 dB
26m ± 0.30m	[1023.62" ± 11.81"]	17-300330-26	0.22 dB
27m ± 0.30m	[1062.99" ± 11.81"]	17-300330-27	0.22 dB
28m ± 0.30m	[1102.36" ± 11.81"]	17-300330-28	0.22 dB
29m ± 0.30m	[1141.73" ± 11.81"]	17-300330-29	0.22 dB
30m ± 0.30m	[1181.10" ± 11.81"]	17-300330-30	0.22 dB
31m ± 0.30m	[1220.47" ± 11.81"]	17-300330-31	0.22 dB
32m ± 0.30m	[1259.84" ± 11.81"]	17-300330-32	0.22 dB
33m ± 0.30m	[1299.21" ± 11.81"]	17-300330-33	0.22 dB
34m ± 0.30m	[1338.58" ± 11.81"]	17-300330-34	0.22 dB
35m ± 0.35m	[1377.95" ± 13.78"]	17-300330-35	0.22 dB
36m ± 0.35m	[1417.32" ± 13.78"]	17-300330-36	0.23 dB
37m ± 0.35m	[1456.69" ± 13.78"]	17-300330-37	0.23 dB
38m ± 0.35m	[1496.06" ± 13.78"]	17-300330-38	0.23 dB
39m ± 0.35m	[1535.43" ± 13.78"]	17-300330-39	0.23 dB
40m ± 0.40m	[1574.80" ± 15.75"]	17-300330-40	0.23 dB

Cable Length L		Part Number	Max. IL
Meters	[Inches]		
41m ± 0.40m	[1614.17" ± 15.75"]	17-300330-41	0.24 dB
42m ± 0.40m	[1653.54" ± 15.75"]	17-300330-42	0.24 dB
43m ± 0.40m	[1692.91" ± 15.75"]	17-300330-43	0.24 dB
44m ± 0.40m	[1732.28" ± 15.75"]	17-300330-44	0.24 dB
45m ± 0.40m	[1771.65" ± 15.75"]	17-300330-45	0.24 dB
46m ± 0.40m	[1811.02" ± 15.75"]	17-300330-46	0.24 dB
47m ± 0.40m	[1850.39" ± 15.75"]	17-300330-47	0.24 dB
48m ± 0.40m	[1889.76" ± 15.75"]	17-300330-48	0.24 dB
49m ± 0.40m	[1929.13" ± 15.75"]	17-300330-49	0.24 dB
50m ± 0.50m	[1968.50" ± 19.69"]	17-300330-50	0.24 dB
51m ± 0.50m	[2007.87" ± 19.69"]	17-300330-51	0.24 dB
52m ± 0.50m	[2047.24" ± 19.69"]	17-300330-52	0.24 dB
53m ± 0.50m	[2086.61" ± 19.69"]	17-300330-53	0.24 dB
54m ± 0.50m	[2125.98" ± 19.69"]	17-300330-54	0.24 dB
55m ± 0.50m	[2165.35" ± 19.69"]	17-300330-55	0.24 dB
56m ± 0.50m	[2204.72" ± 19.69"]	17-300330-56	0.24 dB
57m ± 0.50m	[2244.09" ± 19.69"]	17-300330-57	0.24 dB
58m ± 0.50m	[2283.46" ± 19.69"]	17-300330-58	0.24 dB
59m ± 0.50m	[2322.83" ± 19.69"]	17-300330-59	0.24 dB
60m ± 0.60m	[2362.21" ± 23.62"]	17-300330-60	0.24 dB

Cable Length L		Part Number	Max. IL
Meters	[Inches]		
61m ± 0.60m	[2401.57" ± 23.62"]	17-300330-61	0.25 dB
62m ± 0.60m	[2440.95" ± 23.62"]	17-300330-62	0.25 dB
63m ± 0.60m	[2480.31" ± 23.62"]	17-300330-63	0.25 dB
64m ± 0.60m	[2519.68" ± 23.62"]	17-300330-64	0.25 dB
65m ± 0.60m	[2559.05" ± 23.62"]	17-300330-65	0.25 dB
66m ± 0.60m	[2598.42" ± 23.62"]	17-300330-66	0.25 dB
67m ± 0.60m	[2637.80" ± 23.62"]	17-300330-67	0.25 dB
68m ± 0.60m	[2677.16" ± 23.62"]	17-300330-68	0.25 dB
69m ± 0.60m	[2716.53" ± 23.62"]	17-300330-69	0.25 dB
70m ± 0.70m	[2755.91" ± 27.56"]	17-300330-70	0.25 dB
71m ± 0.70m	[2795.28" ± 27.56"]	17-300330-71	0.25 dB
72m ± 0.70m	[2834.65" ± 27.56"]	17-300330-72	0.25 dB
73m ± 0.70m	[2874.02" ± 27.56"]	17-300330-73	0.25 dB
74m ± 0.70m	[2913.39" ± 27.56"]	17-300330-74	0.25 dB
75m ± 0.70m	[2952.76" ± 27.56"]	17-300330-75	0.25 dB
76m ± 0.70m	[2992.13" ± 27.56"]	17-300330-76	0.25 dB
77m ± 0.70m	[3031.50" ± 27.56"]	17-300330-77	0.25 dB
78m ± 0.70m	[3070.87" ± 27.56"]	17-300330-78	0.25 dB
79m ± 0.70m	[3110.24" ± 27.56"]	17-300330-79	0.25 dB
80m ± 0.80m	[3149.61" ± 31.50"]	17-300330-80	0.25 dB

NOTES:

1. MAXIMUM CONNECTOR INSERTION LOSS (IL): 0.2dB,
PLUS CABLE ATTENUATION OF 0.78dB/km AT 1310nm

2. TEST DATA PROVIDED WITH EACH ASSEMBLY

A ← → B

B ← → A

FIBER PATH DETAIL

Directive 2002/95/EC RoHS Compliant

THIS DRAWING MAY NOT BE COPIED, REPRODUCED, OR REPRODUCED IN ANY WAY AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified			Scale: NTS	Dim. in m [inches]		
	Name	Title	Approval Date							
DOT NOT ALTER CAD DRAWING BY HAND							Material: See Notes			
							Title: IP67 Industrial Duplex LC (ODVA)			
							Single Mode Fiber Optic Patch Cords			
							Nickel Plated Zinc Die-Cast Version			
							Drawing No.: 17K1A239			
							Part No.: SEE TABLE			
							DIN A3			
							Sheet 1/1			

CONEC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[17-300330-07](#) [17-300330-60](#) [17-300330-15](#) [17-300330-40](#) [17-300330-03](#) [17-300330-10](#) [17-300330-30](#) [17-300330-01](#) [17-300330-05](#) [17-300330-02](#) [17-300330-20](#)