


Nylon Round Spacers



- Molded nylon 6/6.
- An excellent insulator, the nylon spacer's surface lubricity allows wires to be routed against spacer without fear of chafing the insulation.
- Natural (milky white) finish.
- Relatively low operating temperature.

SCREW NO.	MAJOR DIA.	HOLE SIZE
#2	0.086	0.093
#3	0.099	0.100
#4	0.112	0.120
#5	0.125	0.130
#6	0.138	0.144
#8	0.164	0.169
#10	0.190	0.196
#12	0.216	0.220

LENGTH		O.D.	HOLE CLEARANCE SIZE					LENGTH		O.D.	HOLE CLEARANCE SIZE				
			#2	#4	#6	#8	#10				#2	#4	#6	#8	#10
0.125	1/8	3/16	9160	9180				.562	9/16	5/16	4065H 4067H 4069H				
		1/4	4000 4001 4002			4068H 4070H									
		5/16	4065A 4067A 4069A												
		3/8	4068A 4070A												
0.187	3/16	3/16	9161	9181				.625	5/8	3/16	9168	9188			
		1/4	4003 4004 4005			4068J 4070J									
		5/16	4065B 4067B 4069B												
		3/8	4068B 4070B												
0.25	1/4	3/16	9162	9182				.687	11/16	3/16	9169	9189			
		1/4	4006 4007 4008			4028 4029									
		5/16	4065C 4067C 4069C			4065K 4067K 4069K									
		3/8	4068C 4070C			4068K 4070K									
0.312	5/16	3/16	9163	9183				.750	3/4	3/16	9170	9190			
		1/4	4009 4010 4011			4031 4032									
		5/16	4065D 4067D 4069D			4065L 4067L 4069L									
		3/8	4068D 4070D			4068L 4070L									
0.375	3/8	3/16	9164	9184				.812	13/16	3/16	9171	9191			
		1/4	4012 4013 4014			4034 4035									
		5/16	4065E 4067E 4069E			4065M 4067M 4069M									
		3/8	4068E 4070E			4068M 4070M									
0.437	7/16	3/16	9165	9185				.875	7/8	3/16	9172	9192			
		1/4	4015 4016 4017			4037 4038									
		5/16	4065F 4067F 4069F			4065N 4067N 4069N									
		3/8	4068F 4070F			4068N 4070N									
0.5	1/2	3/16	9166	9186				.937	15/16	3/16	9173	9193			
		1/4	4018 4019 4020			4041 4042									
		5/16	4065G 4067G 4069G			4065P 4067P 4069P									
		3/8	4068G 4070G			4068P 4070P									
0.562	9/16	3/16	9167	9187				1	1	3/16	9174	9194			
		1/4	4021 4022 4023			4043 4044									
												5/16	4065Q 4067Q 4069Q		
												3/8	4068Q 4070Q		