

Steckhülsen 6,3 mm

Clips femelles

Receptacles


DIN 46247/3

* ausgenommen
* excepté
* excepted

Werkstoff/Matière/Material
.2 = Bronze/bronze
.6 = Messing/laiton/brass
.9 = Stahl/acier/steel

■ = Oberflächen/Surface/Surface-plating
Seite/page/page 5.011


Strombelastbarkeit / Intensité admissible / Current carrying capacity:
0.5 – 1.0 mm² / 10A max.
1.5 – 2.5 mm² / 15A max.
4.0 – 6.0 mm² / 25A max



mm ²	AWG	Grösse Grandeur Size	Artikelnummer Numéro d'article Part-No.	DIN	L1 mm	L2 mm	L3 mm	A1 mm	A2 mm	S mm	Werkzeuge Outils Toolings
0.5-1	22-18	6.3 x 0.8	3831.6 ■	46247/T3	19	7.5	4	8.3	4.5	0.45	3983p.4, 4084.5 3984a, 3988n
	22-18	6.3 x 0.8	3831.9 ■	46247/T3	19	7.5	4	9	4.5	0.45	
0.5-1.5	22-16	6.3 x 0.8	3832.6 ■	46247/T3	19	7.5	4	9	4.5	0.45	3975c, 3983p.4, 3984a, 3988n
	22-16	6.3 x 0.8	3832.9 ■	46247/T3	19	7.5	4	9	4.5	0.45	
1-2.5	18-14	6.3 x 0.8	3833.2 ■	46247/T3	19	7.5	4	8.5	4	0.4	3975c, 3983p.4, 3984a, 3988n
	18-14	6.3 x 0.8	3833.6 ■	46247/T3	19	7.5	4	8.5	4	0.4	
	18-14	6.3 x 0.8	3833.9 ■	46247/T3	19	7.5	4	8.5	4	0.4	
4-6	12-10	6.3 x 0.8	3835a.6 ■	46247/T3	19	7.5	4	9	4.5	0.45	3975c, 3983p.4, 3984b, 3988n

Werkstoff/Matière/Material
.6 = Messing/laiton/brass


■ = Oberflächen/Surface/Surface-plating
Seite/page/page 5.011



mm ²	AWG	Grösse Grandeur Size	Artikelnummer Numéro d'article Part-No.	DIN	L1 mm	L2 mm	L3 mm	A1 mm	A2 mm	S mm	Werkzeuge Outils Toolings
1-2.5	18-14	6.3 x 0.8	3832d.6 ■	46340/T3	19	7.5	7.3	8.5	4	0.4	3975c, 3983p.4, 3984a, 3988n

Werkstoff/Matière/Material
.6 = Messing/laiton/brass
.9 = Stahl/acier/steel

■ = Oberflächen/Surface/Surface-plating
Seite/page/page 5.011



mm ²	AWG	Grösse Grandeur Size	Artikelnummer Numéro d'article Part-No.	DIN	L1 mm	L2 mm	L3 mm	A1 mm	A2 mm	S mm	Werkzeuge Outils Toolings
4-6	12-10	6.3 x 0.8	3835.6 ■	46247/T3	19	7.5	4	9	4.5	0.45	3975c, 3983p.4, 3984b, 3988n
	12-10	6.3 x 0.8	3835.9 ■	46247/T3	19	7.5	4	9	4.5	0.45	