


# 3.5mm Stereo Jack



161-3402-E

KOBICONN

3.5mm Stereo Jack



Circuit Diagram



Dimensions: mm (in.)

## SPECIFICATIONS

|                        |                                           |
|------------------------|-------------------------------------------|
| Type:                  | 3.5mm Stereo, Open Circuit, Chassis Mount |
| Contact Resistance:    | 30mΩ max.                                 |
| Insulation Resistance: | 100MΩ @ 500VDC                            |
| Soldering Temperature: | 210°C max. for 3~5 seconds                |
| Withstand Voltage:     | 500VAC for 1 Minute                       |
| Life Test:             | 5,000 Cycles                              |
| Housing:               | Polyoxymethylene                          |
| Ring, Tip Terminals:   | Silver Plated Phosphor Bronze             |
| Earth Terminal:        | Silver Plated Brass                       |
| Barrel:                | Nickel Plated Brass                       |
| Color:                 | Black                                     |
| Hardware Included:     | Knurled Nut                               |
| RoHS Compliant         |                                           |

Date Last Revised: 3-5-07

Available from Mouser Electronics  
1-800-346-6873 / [www.mouser.com](http://www.mouser.com)

KC-301090

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-3402-E

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-3402-E](#)