


REV.	DESCRIPTION/ECO NO.	DATE
	RELEASED AND CANCEL	10/11/00
	7156, 6805	



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
6835	5.0	.060	.050	0.63	100,000	C-8
7135	5.0	.075	.090	1.13	25,000	C-8
7155	5.0	.115	.150	1.89	40,000	C-8

METRIC		DIMENSIONS ARE IN MILLIMETERS	
		TOLERANCE UNLESS OTHERWISE SPECIFIED	
THIRD ANGLE PROJECTION		1 PL. +/- 0.2	
		2 PL. +/- 0.20	
		ANGLE +/- 0	
DRAWN BY	DATE	APPROVED BY	DATE
L. WENGSTROM	10/11/00	Q.C.	10/11/00
- CAD DRAWING -			
MANUAL REVISIONS NOT PERMITTED			
TITLE			
JKL COMPONENTS CORPORATION			
T-3/4 STANDARD AXIAL LEAD LAMP			
SIZE	FIG. NO.	DRAWING NO.	REV.
A	55335		
SCALE	NONE	RELEASED DATE	REVISION DATE
		10/11/00	
AXIAL STANDARD T-3/4			
REV. NO.			
1 OF 1			