


8				7			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
COPYRIGHT 20				20			
BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.							
PART NUMBER	REV	FIRST USED	POWER UNIT		FEED TYPE	DESCRIPTION	
1852457-1	A	122500-1	LEADMAKER		POST FEED	CUTS CARRIER	
1852457-2	A	565435-5	BENCH MODEL K		PRE FEED	CUTS CARRIER	
1852457-3	A	354500-1	BENCH MODEL G		PRE FEED	CUTS CARRIER	
1852457-6	A	122500-1	LEADMAKER		POST FEED	CONTINUOUS CARRIER	
7-1852457-7	A	-	-		-	SPARE PARTS	

RECOMMENDED SPARE PARTS

GREASE LIGHTLY

GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE



TERMINAL NAME: CENTER TERMINAL					
TE PN	Hirose PN	Hirose TERMINAL - TE CRIMP SPECS			
1949319	GT17-2428SCF	PAD LTR	CRIMP HEIGHT		WIRE SIZE
-	-	A	.028±.002[.71±0.05mm]		24AWG
-	-	B	.026±.002[.66±0.05mm]		26AWG
-	-	C	.025±.002[.64±0.05mm]		28AWG
-	-	D	-		-
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	.042 [1.07mm]	F	24-28 AWG
-	-	INSUL	.050 [1.27mm]	O	.027-.039[0.7-1.0mm]
WIRE STRIP LENGTH	TERM APPL SPEC	FEED	APPLICATOR INSTRUCTIONS		SET UP GAGE
.124 -.139	NONE	.275	408-8040		458637-1

LOC		DIST		REVISIONS			
A		66		P	LTR	DESCRIPTION	DATE
				A		RELEASED	03MAY2007
							LG
							GB

-	2	2	2	2	-	6-354779-4	PIN, WIRE DISC, .3310	128
-	2	2	2	2	-	6-354779-4	PIN, WIRE DISC, .3310	127
-	2	2	2	2	-	6-354779-2	PIN, WIRE DISC, .3300	126
-	-	-	REF	-	..	455749-1	GUARD WINDOW	116
-	-	REF	-	-	..	679532-1	INSERT, GUARD	115
-	1	1	1	1	-	690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112
-	1	1	1	1	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
-	1	1	1	1	-	318563-1	GUARD, FRONT CHIP	89
-	1	1	1	1	-	455888-3	SPACER, CRIMPER	82
-	1	1	1	1	-	4088040	SF APPL INST 408-8040	72
-	1	1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	71
-	1	1	1	1	-	461264-1	PLATE, IDENTIFICATION	67
-	2	2	2	2	-	21017-2	SCREW, DRIVE	66
-	1	1	1	1	-	986950-1	WASHER, FLAT PRECISION	64
-	1	1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
-	1	1	1	1	-	23030-1	SCR, SKT HD CAP 6-32 x .25	62
-	1	1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
-	1	1	1	1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
-	1	1	1	1	-	458537-2	PAWL, FEED	56
-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
-	2	2	2	2	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	53
-	1	1	1	1	-	21018-5	NUT, HEX, REG 6-32	52
-	1	1	1	1	-	811242-2	BUMPER, HOLD DOWN	51
-	1	1	1	1	-	690753-1	SPACER, TONKER	50
-	-	-	-	-	..	690602-6	CAM, PRE FEED, 1 5/8	49
-	-	-	-	-	..	690602-5	CAM, PRE FEED, 1 1/8	48
-	1	-	-	1	-	690501-4	CAM, POST FEED, 1 5/8	47
-	1	1	1	1	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MQCA)	46
-	1	1	1	1	-	690191-1	PLUG,NYLON	45
-	1	1	1	1	-	1-455673-6	RAM, SIDE FEED	44
-	1	1	1	1	-	690125-1	SHIM SUB-ASSY	43
-	1	1	1	1	-	690124-1	WASHER, RAM (.115)	42
-	1	1	1	1	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
-	1	1	1	1	-	23241-6	BALL, STEEL	40
-	1	1	1	1	-	690170-1	SPRING, COMPRESSION	39
-	1	1	1	1	-	690142-1	DISC, INSULATION	38
-	1	1	1	1	-	354777-1	WIRE DISC, ASSEMBLY	37
-	1	1	1	1	-	22480-5	SPRING, COMPRESSION	36
-	1	1	1	1	-	690212-1	POST, RAM	35
-	1	1	1	1	-	690786-1	TERMINAL SUPPORT	34
-	2	2	2	2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
-	1	1	1	1	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
-	1	1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
-	1	1	1	1	-	1320908-9	SPACER, STRIP GUIDE	30
-	1	1	1	1	-	1633091-2	ASSEMBLY, STRIP GUIDE	29
-	1	1	1	1	-	1-455888-0	SPACER, CRIMPER	28
-	1	1	1	1	-	1320928-1	PLATE, STRIP GUIDE	24
-	1	-	-	1	-	690472-2	STRIPPER	22
-	1	1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
-	4	4	4	4	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
-	-	1	1	-	-	691353-1	STRIPPER	19
-	1	-	-	-	-	679625-1	SHEAR HOLDER, FRONT (NO CUT)	17
-	1	1	1	1	-	3-22280-3	SPRING, COMPRESSION	12
-	1	1	1	1	-	690461-1	STOP, SHEAR	11
-	-	1	1	1	-	690459-1	SHEAR HOLDER, FRONT	10
-	1	1	1	1	-	462006-1	FLOATING SHEAR, FRONT	9
-	1	1	1	1	-	8-1633117-0	ANVIL, COMBINATION	8
-	1	1	1	1	-	2-455889-0	DEPRESSOR, SHEAR	5
-	1	1	1	1	-	238011-2	BLOCK, CRIMPER SPACER	4
-	1	1	1	1	-	9-1583690-4	CRIMPER, INSUL O	3
-	1	1	1	1	-	456401-4	CRIMPER, WIRE PREMIUM	1
-	77	-6	-3	-2	-1	U/M	PART NO	DESCRIPTION
-	-	-	-	-	-	-	-	ITEM NO

THIS IS A CUSTOMER DRAWING. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED FOR THE CUSTOMER'S USE ONLY. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT THE WRITTEN PERMISSION OF TYCO ELECTRONICS CORPORATION.				DWN	SEKI	25MAR2007	Tyco Electronics		Tyco Electronics Harrisburg, PA 17105-3608	
CHN				L.GROSS	03MAY2007	NAME		SIDE FEED HDM APPLICATOR		
APVD				G.BAILEY	03MAY2007	PRODUCT SPEC		-		
DIMENSIONS:				TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		-		
INCHES				9 PLC ±.01		-		-		
				1 PLC ±.01		-		-		
				2 PLC ±.01		-		-		
				3 PLC ±.001		-		-		
				4 PLC ±.0001		-		-		
MATERIAL				FINISH		WEIGHT		SIZE		CAGE CODE
-				-		-		A1		00779
								C=		1852457
								SCALE		3:5
								SHEET		1
								OF		1
								REV		A

POST-FEED 1 5/8 STROKE	PRE-FEED 1 1/8 STROKE	PRE-FEED 1 5/8 STROKE
- 1 & - 6	- 2	- 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852457-1](#)