




MATERIAL:

Thermoplastic


TEMPERATURE RANGE:

-Climatic category

-55°/ +125°

COLOUR

Black



Dimensions are in millimeters

Shell size	Number of contacts	A ^{+0.9 -0.2}	B ^{+0.10 0}	C ^{±0.05}	D ^{±0.10}	E ^{±0.10}	F ^{±0.10}	PART NUMBER	PART NUMBER
E	09	30.60	12.50	25	29.00	9.99	9.99	863086B	863086B10
A	15	38.90	12.50	33.32	29.00	11.99	9.99	863021B	863021B10
B	25	52.80	12.50	47.05	35.00	16.40	9.99	863022B	863022B10
C	37	69.10	12.50	63.50	41.00	23.49	9.99	863023B	863023B10
D	50	66.70	15.30	61.10	41.00	23.49	12.79	863024B	863024B10
Packaging per 100 pieces								Packaging per 10 pieces	

European Views

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		mm 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	MASSON	1999/08/16	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 5			
Eng	PESSON	1999/08/16			0.XX	±0.1					
Chr	LEGARE	1999/08/16			0.XXX	±0.1		ECN LS06-0095			
Appr	LEGARE	1999/08/16	Product family				D-SUB	Spec ref -			
			title MONOBLOC PLASTIC HOODS FOR POTTING straight exit					dwg no C01-8655-1530		Rev E	
catalog no			-					CUSTOMER		sheet 1 of 1	

rev	ecn no	dr	date
B	-	JAR	2003/03/07
C	LS05-0026	MPE	2005/07/08
D	LS05-0084	MPE	2005/09/29
E	LS06-0095	LGO	2006/07/24
-	-	-	-
-	-	-	-
-	-	-	-

REV F - 2006-04-17



Copyright FCI.

PDM: Rev:E

STATUS:Released

Printed: Aug 26, 2006