



List Price \$125.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Ampere Rating	1.0A
General Application	Short circuit and overcurrent protection
For Use With	OEM Panels and Enclosures
Voltage Rating	120VAC - 60VDC
Short Circuit Current Rating	5kA@240VAC - 10kA@120VAC
Circuit Breaker Type	Standard
Mounting Type	Flush, Surface or DIN Rail (35mm)
HACR Rated	Yes
Weight	4.40 Ounces
Number of Poles	1-Pole
Marketing Trade Name	Multi 9
Approvals	UL489 Listed - CSA 22.2 #5.1 Certified - IEC Rated 60947-2
Enclosure Rating	IP40
Trip Curve	C Curve - Magnetic operates between 7 to 10 times
Depth	3.00 Inches (76mm)
Type	C60N
Terminal Type	Line: Box Lug - Load: Box Lug
Wire Size	#18 to #4 AWG
Height	4.21 Inches (107mm)
Width	0.71 Inches (18mm)

Shipping and Ordering

Category	00915 -
Discount Schedule	DE2
GTIN	00785901409670
Package Quantity	1
Weight	0.29 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 08/03/2012 07:29:05