

BMP®71 Wire & Cable Materials:

General Adhesive Wire and Cable Markers

- **B-498 Repositionable Vinyl Cloth Material** - Industrial strength and ideal for curved surfaces. Firm adhesive can be removed cleanly and reapplied.
- **B-499 Permanent Nylon Cloth Material** - Durable industrial strength and designed to conform to curved surfaces.




Figure 29




Figure 30




Figure 33



Diagram	Part Number	B#	Material	Color	Approx. Wire Gauge	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels/Roll	Rec. Ribbon
B-498 Repositionable Vinyl Cloth Material									
Fig. 31	M71-7-498	B-498	Vinyl	White	16-10	0.500 (12.700)	0.500 (12.700)	500	M71-R6200
Fig. 31	M71-17-498	B-498	Vinyl	White	12-10	1.000 (25.400)	0.500 (12.700)	500	M71-R6200
Fig. 31	M71-10-498	B-498	Vinyl	White	16-10	0.250 (6.350)	0.750 (19.050)	750	M71-R6200
Fig. 31	BM71-11-498	B-498	Vinyl	White	16-10	0.500 (12.700)	0.750 (19.050)	5000	M71-R6200
Fig. 31	M71-11-498	B-498	Vinyl	White	16-10	0.500 (12.700)	0.750 (19.050)	500	M71-R6200
Fig. 31	M71-16-498	B-498	Vinyl	White	12-10	0.375 (9.530)	1.000 (25.400)	500	M71-R6200
Fig. 31	BM71-18-498	B-498	Vinyl	White	12-10	0.750 (19.050)	1.000 (25.400)	2500	M71-R6200
Fig. 31	M71-18-498	B-498	Vinyl	White	12-10	0.750 (19.050)	1.000 (25.400)	250	M71-R6200
Fig. 31	BM71-19-498	B-498	Vinyl	White	12-10	1.000 (25.400)	1.000 (25.400)	2500	M71-R6200
Fig. 31	M71-19-498	B-498	Vinyl	White	12-10	1.000 (25.400)	1.000 (25.400)	250	M71-R6200
Fig. 31	BM71-29-498	B-498	Vinyl	White	10-4	0.500 (12.700)	1.500 (38.100)	5000	M71-R6200
Fig. 31	M71-29-498	B-498	Vinyl	White	10-4	0.500 (12.700)	1.500 (38.100)	500	M71-R6200
Fig. 31	M71-30-498	B-498	Vinyl	White	10-4	0.750 (19.050)	1.500 (38.100)	250	M71-R6200
Fig. 31	M71-31-498	B-498	Vinyl	White	10-4	1.000 (25.400)	1.500 (38.100)	250	M71-R6200
Fig. 31	M71-32-498	B-498	Vinyl	White	10-4	1.500 (38.100)	1.500 (38.100)	250	M71-R6200
Fig. 31	M71-21-498	B-498	Vinyl	White	Cables	1.000 (25.400)	2.500 (63.500)	100	M71-R6200
Fig. 31	M71-33-498	B-498	Vinyl	White	Cables	1.500 (38.100)	4.000 (101.600)	100	M71-R6200
Fig. 33	BM71C-240-498	B-498	Vinyl	White	—	0.240 (6.096)	275 ft. (83.82 m)	1 Roll (cont.)	M71-R6200
Fig. 30	BM71C-318-498	B-498	Vinyl	White	—	0.318 (8.070)	275 ft. (83.82 m)	1 Roll (cont.)	M71-R6200
Fig. 30	BM71C-375-498	B-498	Vinyl	White	—	0.375 (9.530)	275 ft. (83.82 m)	1 Roll (cont.)	M71-R6200
Fig. 30	M71C-240-498	B-498	Vinyl	White	—	0.240 (6.096)	30 ft. (9.10 m)	1 Roll (cont.)	M71-R6200
Fig. 30	M71C-318-498	B-498	Vinyl	White	—	0.318 (8.070)	30 ft. (9.10 m)	1 Roll (cont.)	M71-R6200
Fig. 30	M71C-375-498	B-498	Vinyl	White	—	0.375 (9.530)	30 ft. (9.10 m)	1 Roll (cont.)	M71-R6200
Fig. 33	M71C-500-498	B-498	Vinyl	White	—	0.500 (12.700)	30 ft. (9.10 m)	1 Roll (cont.)	M71-R6200
Fig. 33	M71C-1000-498	B-498	Vinyl	White	—	1.000 (25.400)	30 ft. (9.10 m)	1 Roll (cont.)	M71-R6200
Fig. 33	M71C-1900-498	B-498	Vinyl	White	—	1.900 (48.300)	30 ft. (9.10 m)	1 Roll (cont.)	M71-R6200
B-499 Permanent Nylon Cloth Material									
Fig. 31	M71-7-499	B-499	Nylon Cloth	White	16-10	0.500 (12.700)	0.500 (12.700)	500	M71-R4300
Fig. 31	BM71-11-499	B-499	Nylon Cloth	White	16-10	0.500 (12.700)	0.750 (19.050)	5000	M71-R4300
Fig. 31	M71-11-499	B-499	Nylon Cloth	White	16-10	0.500 (12.700)	0.750 (19.050)	500	M71-R4300
Fig. 31	M71-16-499	B-499	Nylon Cloth	White	12-10	0.375 (9.530)	1.000 (25.400)	500	M71-R4300
Fig. 31	M71-18-499	B-499	Nylon Cloth	White	12-10	0.750 (19.050)	1.000 (25.400)	250	M71-R4300
Fig. 31	M71-19-499	B-499	Nylon Cloth	White	12-10	1.000 (25.400)	1.000 (25.400)	250	M71-R4300
Fig. 29	M71-78-499	B-499	Nylon Cloth	White	12-10	1.900 (48.260)	1.000 (25.400)	250	M71-R4300
Fig. 31	M71-28-499	B-499	Nylon Cloth	White	10-4	0.250 (6.350)	1.500 (38.100)	750	M71-R4300
Fig. 31	M71-29-499	B-499	Nylon Cloth	White	10-4	0.500 (12.700)	1.500 (38.100)	500	M71-R4300
Fig. 31	M71-30-499	B-499	Nylon Cloth	White	10-4	0.750 (19.050)	1.500 (38.100)	250	M71-R4300
Fig. 31	M71-31-499	B-499	Nylon Cloth	White	10-4	1.000 (25.400)	1.500 (38.100)	250	M71-R4300
Fig. 31	M71-21-499	B-499	Nylon Cloth	White	Cables	1.000 (25.400)	2.500 (63.500)	100	M71-R4300
Fig. 33	M71C-500-499	B-499	Nylon Cloth	White	—	0.500 (12.700)	30 ft. (9.10 m)	1 Roll (cont.)	M71-R4300
Fig. 33	M71C-1000-499	B-499	Nylon Cloth	White	—	1.000 (25.400)	30 ft. (9.10 m)	1 Roll (cont.)	M71-R4300
Fig. 33	M71C-1900-499	B-499	Nylon Cloth	White	—	1.900 (48.300)	30 ft. (9.10 m)	1 Roll (cont.)	M71-R4300

* "B" indicates bulk roll.

Approx. wire gauge based on AWG for THHN wire.



Did You Know? www.BradyID.com

Visit BradyID.com for online ordering and instant access to:

- Product Info
- Product Demos
- Custom Orders
- Whitepapers
- Webinars
- And More!

