



AC Compact Fan Kits

Kits incorporating a range of AC fans, a power lead and either a metal guard or an air filter option.

- 230V fans
- Can be operated at 50 or 60Hz
- Metal fan housings
- IP20 Protection
- Lead 610mm
- Filter pads that can be changed without switching off the fan

Part Number	Airflow	Airflow	Voltage	Noise	Bearings	Power	Speed	Temperature Range	Length	Width	Depth	Fan Type	Lead	Guard	Filter
	M3/h	CFM	V	dB(A)		W	RPM	°C	mm	mm	mm				
9956L-KR0	84	49.4	230	29	BB	9.5	1850	-40...+80	119	119	25	9956L	LZ120/1.5	LZ30K	-
9956L-KR1	84	49.4	230	29	BB	9.5	1850	-40...+80	119	119	25	9956L	LZ120/1.5	-	PMFA120T
9956-KR0	117	68.9	230	37	BB	14.0	2450	-40...+70	119	119	25	9956	LZ120/1.5	LZ30K	-
9956-KR1	117	68.9	230	37	BB	14.0	2450	-40...+70	119	119	25	9956	LZ120/1.5	-	PMFA120T
4890N-KR0	80	47.1	230	25	SB	11.0	1550	-10...+70	119	119	38	4890N	LZ120/1.5	LZ30K	-
4890N-KR1	80	47.1	230	25	SB	11.0	1550	-10...+70	119	119	38	4890N	LZ120/1.5	-	PMFA120T
4850N-KR0	100	58.9	230	32	SB	10.0	1800	-10...+70	119	119	38	4850N	LZ120/1.5	LZ30K	-
4850N-KR1	100	58.9	230	32	SB	10.0	1800	-10...+70	119	119	38	4850N	LZ120/1.5	-	PMFA120T
4650N-KR0	160	94.2	230	46	SB	19.0	2650	-10...+55	119	119	38	4650N	LZ120/1.5	LZ30K	-
4650N-KR1	160	94.2	230	46	SB	19.0	2650	-10...+55	119	119	38	4650N	LZ120/1.5	-	PMFA120T
4656N-KR0	160	94.2	230	47	BB	19.0	2650	-40...+85	119	119	38	4656N	LZ120/1.5	LZ30K	-
4656N-KR1	160	94.2	230	47	BB	19.0	2650	-40...+85	119	119	38	4656N	LZ120/1.5	-	PMFA120T
4600N-KR0	180	105.9	115	50	SB	18.0	3100	-10...+60	119	119	38	4600N	LZ120/1.5	LZ30K	-
4600N-KR1	180	105.9	115	50	SB	18.0	3100	-10...+60	119	119	38	4600N	LZ120/1.5	-	PMFA120T
4606N-KR0	160	94.2	115	46	SB	19.0	2650	-10...+55	119	119	38	4606N	LZ120/1.5	LZ30K	-
4606N-KR1	160	94.2	115	46	SB	19.0	2650	-10...+55	119	119	38	4606N	LZ120/1.5	-	PMFA120T
ACI4420HH-KR0	180	105.9	230	42	BB	4.4	3350	-20...+75	119	119	38	ACI4420HH	LZ120/1.5	LZ30K	-
ACI4420HH-KR1	180	105.9	230	42	BB	4.4	3350	-20...+75	119	119	38	ACI4420HH	LZ120/1.5	-	PMFA120T
W2E142-BB01-01-KR0	330	194	230	52	BB	29.0	2800	-25...+55	150	172	38	W2E142-BB01-01	LZ120/1.5	03749-2-4039	-
W2E142-BB01-01-KR1	330	194	230	52	BB	29.0	2800	-25...+55	150	172	38	W2E142-BB01-01	LZ120/1.5	-	PMFA160