


## Snap-In Clips


- Clip around bundle to hold securely in place
- Clips are placed on the bundle then attached to the panel
- Material: Nylon 6.6
- For indoor use only




| Part Number | Max. Bundle Diameter |      | Height A |      | Max. Panel Thickness |     | Panel Hole Diameter |     | Color   | Mounting Method | Std. Pkg. Qty. | Std. Ctn. Qty. |
|-------------|----------------------|------|----------|------|----------------------|-----|---------------------|-----|---------|-----------------|----------------|----------------|
|             | In.                  | mm   | In.      | mm   | In.                  | mm  | In.                 | mm  |         |                 |                |                |
| SICH25-C    | .25                  | 6.4  | .40      | 20.9 | .10                  | 2.5 | .25                 | 6.4 | Natural | Push Barb       | 100            | 500            |
| SICH38-C    | .38                  | 9.7  | .54      | 24.9 | .10                  | 2.5 | .25                 | 6.4 |         |                 | 100            | 500            |
| SICH50-C    | .50                  | 12.7 | .67      | 28.2 | .10                  | 2.5 | .25                 | 6.4 |         |                 | 100            | 500            |
| SICH75-C    | .75                  | 19.1 | .96      | 35.6 | .10                  | 2.5 | .25                 | 6.4 |         |                 | 100            | 500            |
| SICH100-C   | 1.00                 | 25.4 | 1.21     | 41.9 | .10                  | 2.5 | .25                 | 6.4 |         |                 | 100            | 500            |
| SICH150-C   | 1.50                 | 38.0 | 1.71     | 54.6 | .10                  | 2.5 | .25                 | 6.4 |         |                 | 100            | 500            |

## Wire Saddles

- Funnel entry design for fast insertion of wires and cables
- Available in vertical and horizontal loading configurations
- Design of wing provides added stability
- Material: Nylon 6.6
- For indoor use only



VWS Vertical



HWS Horizontal

| Part Number | Max. Bundle Capacity |             | Height A |      | Width B |      | Max. Panel Thickness |     | Panel Hole Diameter |     | Color   | Mounting Method | Std. Pkg. Qty. | Std. Ctn. Qty. |
|-------------|----------------------|-------------|----------|------|---------|------|----------------------|-----|---------------------|-----|---------|-----------------|----------------|----------------|
|             | In.                  | mm          | In.      | mm   | In.     | mm   | In.                  | mm  | In.                 | mm  |         |                 |                |                |
| VWS4218-C   | 0.18 x 0.42          | 5.0 x 10.7  | 0.58     | 14.7 | 0.60    | 15.2 | 0.08                 | 2.0 | 0.19                | 4.7 | Natural | Push Barb       | 100            | 500            |
| VWS4238-C   | 0.40 x 0.42          | 10.2 x 10.7 | 0.78     | 19.8 | 0.60    | 15.2 | 0.08                 | 2.0 | 0.19                | 4.7 |         |                 | 100            | 500            |
| VWS4274-C   | 0.74 x 0.42          | 19.0 x 10.7 | 1.14     | 29.0 | 0.60    | 15.2 | 0.08                 | 2.0 | 0.19                | 4.7 |         |                 | 100            | 500            |
| VWS42105-C  | 1.05 x .42           | 27.0 x 10.7 | 1.45     | 36.8 | 0.60    | 15.2 | 0.08                 | 2.0 | 0.19                | 4.7 |         |                 | 100            | 1000           |
| HWS2819-C   | 0.19 x 0.28          | 5.0 x 7.1   | 0.42     | 10.7 | 0.44    | 11.2 | 0.08                 | 2.0 | 0.19                | 4.7 |         |                 | 100            | 500            |