

PRODUCT DATASHEET

2D Magnet Light
Energizer®
INDUSTRIAL

E251Y

CONVENIENT

- Built in magnet for mounting on metal surfaces
- Flip-up hanger ring is always there when you need it



BRIGHT

- Krypton bulb delivers 17 lumens
- Shatterproof lens



ANTI-ROLL

- Stays where you put it



DURABLE

- Survives 1-meter drop test
- Shatterproof lens



A great choice for general lighting needs, the Energizer® Industrial 2D Magnet Light features a flip-up hook that allows hanging or belt-carrying the light easily. It also has a magnet on the body, giving you the ability to fix it to a toolbox or any other metal surface.

This light has a sturdy polyethylene case and a shatterproof lens to protect interior components from damage on the job. In addition, the anti-roll feature helps keep the light in place when you set it down.




Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation:	Energizer Industrial 2D Magnet Light
Model:	E251Y
Color:	Yellow
Power Source:	Two "D"
ANSI/NEDA:	Series 13D
Lamp:	KPR-102
Lamp Rating:	2.4V, 0.7A
Lamp Life (hr):	15
Lamp Output (lumens):	17
Beam Distance (m):	120
Peak Beam Intensity (cd):	3,700
Run Time (h:mm):	2:30
Typical Weight:	139 grams without batteries
Dimensions (mm):	208 x 60

Performance:



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
©Energizer / All Rights Reserved