

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0190690209
Status: Active
Description: Krimptite™ Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 10, Length 19.94mm (.785")

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Ring and Spade Terminals
Series 19069
Mil-Spec N/A
Product Name Krimptite™
Type Ring

Physical
Barrel Type Closed
Insulation None
Material - Plating Mating Tin
Packaging Type Bag
Plating min: Mating (µin) 100
Plating min: Mating (µm) 2.5
Plating min: Termination (µin) 100
Plating min: Termination (µm) 2.5
Stud Size 10 (M5)
Wire Size AWG 10, 12
Wire Size mm² 4.00 - 6.00

Electrical
CSA LR18689
UL E32244

Material Info
Old Part Number C-128-10

Reference - Drawing Numbers
Sales Drawing CCD10101



Series
image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Halogen-Free
Status
Halogen-Free



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19069Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640070100
Hand Crimp Tool	0640030100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION