





(1,27 mm) .050"


TOLC-120-12-F-Q-LC



TOLC-140-02-F-Q-A



TOLC-120-02-L-Q-LC



TOLC SERIES

QUAD ROW SMT TERMINAL

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?TOLC

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au over 50µ" (1,27 µm) Ni

Current Rating:

2.4 A per pin

(6 adjacent pins powered)

Operating Temp Range:

-55°C to +125°C

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:


Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max (05-30)

(0,15 mm) .006" max (35-50)

Mates with:
SOLC



Drop-in replacement
for FOLC/MOLC when
mated with SOLC

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality



FILE NO. E111594

OTHER SOLUTIONS

- For Micro Rugged, see the MOLC/FOLC pages located in the Tiger Eye™ section.

ALSO AVAILABLE (MOQ Required)

- Other sizes
 - Other platings
- Contact Samtec.

TAPE & REEL AVAILABILITY

No tooling charges.
Minimum order is the lesser of
a full reel quantity or 125 pieces.
Order any quantity above minimum.
In-house design, manufacture.
Quick turn-around.

Call Samtec for specifications
and ordering information.

Note: Some sizes, styles and
options are non-standard,
non-returnable.

TOLC

1

NO. PINS
PER ROWLEAD
STYLEPLATING
OPTION

Q

OPTION

05, 10, 15, 20, 25,
30, 35, 40, 45, 50
(Standard sizes)

Specify
LEAD
STYLE
from
chart

—F
= Gold flash on post,
Gold flash on tail



—L
= 10µ" (0,25 µm)
Gold on post,
Gold flash on tail

—A
= Alignment Pin
(Not available with -LC)


—LC
= Locking Clip
(Not available with -A)
(Manual placement
required)

—K
= (9,00 mm) .354" DIA
Polyimide film
Pick & Place Pad

—TR
= Tape & Reel



LEAD STYLE	A	MATED HEIGHT
-02	(5,59) .220	(6,35) .250
-12	(7,24) .285	(8,00) .315
-22	(9,25) .364	(10,00) .394
-32	(11,23) .442	(12,00) .472



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685