

Rapid Charger

North American Region

[Download User Manual](#)


FAST

- Batteries ready for use in ~15 minutes (2300 mAh AA)



CONVENIENT

- Charge In Car
- Charge At Home



Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Best used with Energizer NiMH batteries.

Note: Batteries may become hot to the touch while charging.

Product Detail:

Designation: Rapid Charger

Color: Black

Charge Capability: "AA" (1) to (4) "AAA" (1) to (4)

Charging Time: (estimate)	Battery (NiMH)	Capacity (mAh)	Qty.	Estimated (time)
	AA	1400	(1-2) (3-4)	10 Min 20 Min
	AA	1500	(1-2) (3-4)	11 Min 22 Min
	AA	2000	(1-2) (3-4)	13 Min 26 Min
	AA	2300	(1-2) (3-4)	15 Min 30 Min
	AA	2450	(1-2) (3-4)	16 Min 32 Min
	AAA	500	(1-2) (3-4)	09 Min 18 Min
	AAA	700	(1-2) (3-4)	12 Min 24 Min
	AAA	850	(1-2) (3-4)	15 Min 30 Min
	AAA	1000	(1-2) (3-4)	17 Min 34 Min

Note: Batteries will not be damaged if left in charger for a longer time.

Trickle Charge : "AA" 50 mA, "AAA" 20 mA

Shutoff Mechanism: Delta V Detection
Temperature Detection
Timer Control

Charger Input: DC 11-16V

AC Adapter Input: 100-120vac 50/60Hz

Weight (charger): 180 grams (6.3 oz.)

Dimensions (mm): 36 x 120 x 80 (H x L x W)

Volume (cm³): 3456 (charger), 2588 (AC Adapter) 1792 (Car)

Rev Polarity Protection: Yes

Primary Battery Detection: Yes

LED Indication: Yes

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc.

Contents herein do not constitute a warranty.



Energizer