






8			7		
THIS DRAWING IS UNPUBLISHED.			RELEASED FOR PUBLICATION		
20			20		
(C) COPYRIGHT 20			BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.		
PART NUMBER	REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION
1855043-1	A	122500-1	LEADMAKER	POST FEED	CUTS CARRIER
1855043-2	A	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER
1855043-3	A	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER
1855043-6	A	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER
7-1855043-7	A	-	-	-	SPARE PARTS



TERMINAL NAME: WIRE SNAP ON FEMALE					
AMP PN	-	AMP TERMINAL - AMP CRIMP SPECS			
3-1438230-4	-				
-	-	REF SETTINGS	CRIMP HEIGHT	WIRE SIZE	
-	-	C3	.059±.002[1.50±0.05mm]	18 AWG	
-	-	D0	.055±.002[1.40±0.05mm]	20 AWG	
-	-	-	-	-	
-	-	-	-	-	
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	.080 [2.03mm]	F	20-18 AWG
-	-	INSUL	.090 [2.29mm]	O	Ø.090 MAX
WIRE STRIP LENGTH	TERM APPL SPEC		FEED	APPL INSTRUCTIONS	SET UP GAGE
.202 - .232	NONE		.731	408-8040	458637-1

LOC		DIST		REVISIONS					
A		66		P	LTR	DESCRIPTION	DATE	DWN	APVD
				A		RELEASED	31MAR2006	RK	TE

- △ RECOMMENDED SPARE PARTS
- △ GREASE LIGHTLY
- △ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE



3	-	-	-	REF	-	...	455749-1	GUARD WINDOW	116
3	-	-	REF	-	-	...	679532-1	INSERT, GUARD	115
	-	1	1	1	1	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
	-	1	1	1	1	-	318563-1	GUARD, FRONT CHIP	89
	-	1	1	1	1	-	4088040	SF APPL INST 408-8040	72
	-	1	1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	71
	-	1	1	1	1	-	461264-5	PLATE, IDENTIFICATION	67
	-	2	2	2	2	-	21017-2	SCREW, DRIVE	66
	-	1	1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
	-	1	1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
	-	1	1	1	1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
	-	1	1	1	1	-	458537-2	PAWL, FEED	56
	-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
	-	2	2	2	2	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	53
	-	1	1	1	1	-	21018-5	NUT, HEX, REG 6-32	52
	-	1	1	1	1	-	811242-2	BUMPER, HOLD DOWN	51
	-	1	1	1	1	-	690753-1	SPACER, TONKER	50
	-	-	1	-	-	...	690602-6	CAM, PRE FEED, 1 5/8	49
	-	-	-	1	-	...	690602-5	CAM, PRE FEED, 1 1/8	48
	-	1	-	-	1	-	690501-4	CAM, POST FEED, 1 5/8	47
	-	1	1	1	1	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MQCA)	46
	-	1	1	1	1	-	690191-1	PLUG, NYLON	45
	-	1	1	1	1	-	455673-1	RAM, SIDE FEED	44
	-	1	1	1	1	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
	-	1	1	1	1	-	690125-1	SHIM SUB-ASSY	39
	-	1	1	1	1	-	1-469367-0	SHIM	38
	-	1	1	1	1	-	879103-3	FINE ADJUST HEAD SUBASSY	37
	-	1	1	1	1	-	2-690786-3	TERMINAL SUPPORT	34
	-	2	2	2	2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
	-	1	1	1	1	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
	-	1	1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
	-	1	1	1	1	-	1320908-1	SPACER, STRIP GUIDE	30
	-	1	1	1	1	-	1633091-2	ASSEMBLY, STRIP GUIDE	29
	-	1	1	1	1	-	455888-6	SPACER, CRIMPER	28
	-	1	1	1	1	-	1320928-1	PLATE, STRIP GUIDE	24
	-	1	-	-	1	-	690472-2	STRIPPER	22
	-	1	1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
	-	4	4	4	4	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
	-	1	1	1	-	-	691353-1	STRIPPER	19
△	-	1	-	-	-	-	679625-1	SHEAR HOLDER, FRONT (NO CUT)	17
	-	1	1	1	1	-	3-22280-3	SPRING, COMPRESSION	12
	-	1	1	1	1	-	690461-1	STOP, SHEAR	11
△	-	-	1	1	1	-	690459-1	SHEAR HOLDER, FRONT	10
△	-	1	1	1	1	-	1-454276-9	FLOATING SHEAR, FRONT	9
△	1	1	1	1	1	-	5-662186-6	ANVIL, COMBINATION	8
	-	1	1	1	1	-	3-455889-3	DEPRESSOR, SHEAR	5
	-	1	1	1	1	-	238011-2	BLOCK, CRIMPER SPACER	4
△	1	1	1	1	1	-	1-456135-4	CRIMPER, INSULATION O PREMIUM	3
	-	1	1	1	1	-	455888-4	SPACER, CRIMPER	2
△	1	1	1	1	1	-	1-456405-3	CRIMPER, WIRE PREMIUM	1
-77 -6 -3 -2 -1 U/M PART NO								DESCRIPTION	ITEM NO

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN		Tyco Electronics	
INCHES		9 PLC ±.01		DR. KNEPPER		Harrisburg, PA 17105-3608	
1 PLC ±.01		2 PLC ±.01		T. ELBIN		31MAR2006	
3 PLC ±.001		4 PLC ±.0001		T. BENCHOFF		31MAR2006	
MATERIAL		FINISH		PRODUCT SPEC		NAME	
-		-		APPLICATION SPEC		SIZE	
-		-		WEIGHT		CAGE CODE	
-		-		CUSTOMER DRAWING		DRAWING NO	
-		-		SCALE		SHEET	
-		-		REV		A	

CUSTOMER VIEWABLE ASSEMBLY