




Dimensions are in millimeters

Shell size	Number of contacts	A ^{+0.76/0}	B ^{+0.25/0}	C ±0.12	F ^{+0.51/0}	G ^{+0.25/0}	H ^{+0.51/0}	L ^{+0.22/0}	M ±0.20	Part number
E	09	30.43	16.46	24.99	10.64	6.05	19.02	0.80	14.80	DEPV09P500TX
A	15	38.76	24.54	33.32	10.64	6.05	27.25	0.80	14.80	DAPV15P500TX
B	25	52.65	38.25	47.04	10.64	6.05	41.02	0.80	14.80	DBPV25P500TX
C	37	68.94	54.71	63.50	10.64	6.05	57.45	0.80	14.80	DCPV37P500TX

NOTES

Materiel and finish:

Housings:

Shells: steel, bright tin plated

Insulators: glass filled thermoplastic UL94V0

Contacts:

brass, 0.40 µg gold plated over nickel


on mating end, bright tin plated over nickel

on termination end

Brackets: glass filled thermoplastic UL94V0

Screwlock: brass, bright tin plated

PC BOARD LAYOUT



a	15/03/01	Creation of drawing	--
ISS	DATE	Lastest modification by : --	MOD N°
Designed by: JARRY date: 15/03/01		Type of drawing: CLIENT	
Checked by: FONTENEAU date: 15/03/01		Released by: --	
TITLE : PINS CONNECTORS D SUB. RIGHT ANGLED SPILL WITH PLASTIC BRACKETS			
SCALE 1.5	Special mfg: -- item list n°: --	MATERIAL: --	N°: --
	General Linear Tolerances: --	General machining -- surface texture: ☒	Geometrical Tolerances see NF E 04-552
	SHEET 1/1		
	FRAMATOME CONNECTORS FRANCE Rue Louis Breguet - BP 05 72024 LE MANS Cedex Tel. 33 (16) 43.84.08.43		This document is the property of FRAMATOME CONNECTORS FRANCE It must not be reproduced or communicated without permission in writing Flow the owners
	FORMAT A3	SOURIAU DRG N° C01-8637-1550	
PROJECT M94D001			