

UniBond

Power Tape

Issued: 24-May-10

Ref: UT4000

Product Description	Typical Technical Data	Application
Heavy duty, strong, tough and 100% waterproof, multi-purpose cloth tape.		Hundreds of uses around the home, garden, garage and workplace.
Carrier: Polyethylene reinforcement with polyester fabric scrim.	Colours: Silver, black, white	
	Thickness: 210 µm	Fixes, binds, mounts, repairs, bundles, joins, seals, reinforces, protects and identifies.
Adhesive: Extra high strength synthetic rubber.	Width: 50mm	
	Tensile Strength (N/cm): 41	Suitable for interior and exterior use.
	Elongation at break (%): 25	Sticks to damp or wet surfaces*, jet-wash proof.
	Peel adhesion (N/cm): 22	Easy to tear by hand.
	Unwind force (N/cm): 3	Limitations: Not intended for permanent repairs. Not suitable for use on glass.
	Temperature range °C: -5 to + 70	*Only sticks to damp or wet non-porous surfaces. The adhesion to wet surfaces is lower than to comparable dry surfaces. Not suitable for total immersion in water.

The above data and performance characteristics are compiled on the results of tests and estimates based on careful calculations. They are put forward in good faith but are not guaranteed. In particular the customer should satisfy himself of the suitability of the product for its intended use and consult us if he is in any doubt about any particular application.

The conditions under which this product is stored affect its performance. Storage should be in dry well ventilated rooms with a reasonably consistent temperature around 20°C and protected from continuous exposure to direct sunlight. The product should always be applied to clean dry surfaces.