



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SP688-*	.047 LB/10 PCS (21.4 g/10 PCS)

NOTES:

1. MATERIAL: HOUSING, LOAD BAR, DIVIDER, STRAIN COLLAR - THERMOPLASTIC UL94V-0 RATED; STRAIN RELIEF BOOT - CLEAR PVC; CONTACT TERMINAL - PHOSPHOR BRONZE ELECTRO-POLISHED AND PLATED WITH .000050" MIN. GOLD IN MATING AREA, GOLD FLASH OVER REMAINDER, .000100" MIN. NICKEL UNDERPLATE.
2. PLUG ACCEPTS 4 PAIR CABLE .225-.250" DIA. WITH 23-24 AWG CONDUCTORS WITH A MAXIMUM INSULATOR DIAMETER OF .040".
3. MEETS DIMENSIONAL REQUIREMENTS OF FCC PART 68 AND IEC 60603-7. ALL DIMENSIONS MAXIMUM UNLESS OTHERWISE SPECIFIED.
4. TERMINATED CONTACT HEIGHT DIMENSION: .237±.005".
5. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE PACKAGE QUANTITY.



PART NUMBER		SP688 - *	
TITLE			
TX6 PLUS MODULAR PLUG FOR CATEGORY 6 PATCH CORDS			
CUSTOMER DRAWING			
ITEM REVISION NAME		M01185CC/06	
DATASET FILE NAME		M01185CC-DC15/06D	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		PANDUIT MATERIAL: SEE NOTE 1 DRAWING NUMBER: 01185-15	
.x ± .xxx ± .010 [.3] .xx ± .03 [.8] ANGLES ±			
THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
MDJr	9-30-02	NGM	NONE
SHT 1 OF 1			SIZE A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
7	6-10-16	BJN	SIP	SASK	UPDATED	01185-15
6	5-14-14	BJN	EJH	EJH	REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY	01185-15