




4513 FP

Very Robust Transponder Coil



Typical L vs Frequency



Part No	Inductance L (mH)	f_L (kHz)	Tol $\pm$ (%)	Q min	f_Q (kHz)	SRF typ (kHz)	DCR max (Ω)	Sensitivity (mV/ μ T)
4513FP-401K-04	0.40	125	10	20	125	6340	11.5	8
4513FP-102K-04	1.00	125	10	20	125	4150	29.0	14
4513FP-242K-04	2.38	125	10	24	125	900	55.0	25
4513FP-492K-04	4.90	125	10	24	125	500	103.0	42
4513FP-722K-04	7.20	125	10	25	125	450	128.0	60
4513FP-902K-04	9.00	125	10	23	125	400	150.0	80
4513FP-103K-04	10.00	125	10	20	125	265	150.0	82

Material : Plastic & Ferrite

SPQ : Reel 3000 [-04]

1000 [-08]

Remark: 2% and 5% tolerance available on request.