



General ordering data

Order No.	0661360000
Part designation	EK 10/35
Version	Earth terminal, 10 mm ² , Screw connection, PA 66, green/yellow, TS 35
EAN	4008190080594
Qty.	100 pc(s).

Additional technical data

Colour of insulating material	green/yellow
Connection direction	on side
End plate required	No
Explosion-tested version "Ex e"	Yes
Installation advice	TS 35
Insulating material	PA 66
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	2
Open sides	closed
Operating temperature range	- 50 °C, + 100 °C
Product family	SAK Series
Type of connection	Screwed
Type of mounting	Screwed
UL 94 flammability rating of insulation material	V2
Version	PE terminal

CSA rating data

Min. cross-section (CSA)	AWG 14
Max. cross-section (CSA)	AWG 6

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	10 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.5 mm ²
Clamping range, max.	10 mm ²
Type of connection	Screw connection
2nd type of connection	screwed

Conductors for clamping (rated connection)

Connection direction	on side
No. of connections	2
Stripping length	12 mm
Clamping screw	M 4
Blade size	1.0 x 5.5 mm
Tightening torque range	1.2...2.4 Nm
Gauge to IEC 60947-1	B6
Solid, min.	0.5 mm ²
Solid, max.	10 mm ²
Stranded, min.	1.5 mm ²
Stranded, max.	6 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	10 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	10 mm ²
AWG conductor size, min.	AWG 20
AWG conductor size, max.	AWG 8
AWG conductor size, min.	0.52 mm ²
AWG conductor size, max.	8.37 mm ²

Dimensions

Width	10 mm
Height of lowest version	45 mm
Length	56 mm
TS 32 offset	3 mm
TS 35 offset	28 mm

PE rating data

Centre screw on PE terminals	M 3
PEN function	No
Pollution severity	3
Rated cross-section	10 mm ²
Rated impulse withstand voltage to adjacent terminal	8 kV
Rated short-time current	1200 A (10 mm ²)
Rated voltage for adjacent terminal	800 V
Standards	IEC 60947-7-2
Tightening torque range for fixing screw	0.5...1.0 Nm

Rating data

Rated cross-section	10 mm ²
Standards	IEC 60947-7-2
Pollution severity	3

UL rating data

Min. cross-section (UL)	AWG 14
Max. cross-section (UL)	AWG 6

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000901
ETIM 3.0	EC000901
eClass 4.1	27-14-03-05
eClass 5.0	27-14-03-05
eClass 5.1	27-14-03-05

Similar products

Order No.	Part designation	Version
0661060000	EK 2.5/35	Earth terminal, 2.5 mm ² , Screw connection, PA 66, green/yellow, TS 35
0661160000	EK 4/35	Earth terminal, 4 mm ² , Screw connection, PA 66, green/yellow, TS 35
0661260000	EK 6/35	Earth terminal, 6 mm ² , Screw connection, PA 66, green/yellow, TS 35
0190160000	EK 16/35	Earth terminal, 16 mm ² , Screw connection, PA 66, green/yellow, TS 35
0661460000	EK 35/35	Earth terminal, 35 mm ² , Screw connection, PA 66, green/yellow, TS 35
1338300000	EK 70/35/M.2ZB O.IK	Earth terminal, 70 mm ² , Screw connection, green/yellow, TS 35
0535300000	EK 95/35/1ZB BK	Earth terminal, 95 mm ² , Screw connection, green/yellow, TS 35
0535400000	EK 95/35/2ZB BK	Earth terminal, 95 mm ² , Screw connection, TS 35