





NOTES:

1. INSULATOR MATERIAL: PBT 30% GLASS FIBER
2. CONTACT MATERIAL: PHOSPHOR BRONZE
3. PLATING: SEE PART NUMBER CODING
4. OPERATING TEMPERATURE: -45°C TO +105°C
5. UL FLAMMABILITY RATING: 94V-0
6. CURRENT RATING: 1 AMP PER CONTACT
7. INSULATION RESISTANCE: 1,000M OHMS MIN.
8. DIELECTRIC WITHSTANDING: 500 VAC
9. MATES WITH SBH21 SERIES
10. FOR .039"[1.00mm] PITCH FLAT CABLE, 26 - 28 AWG WIRE RANGE
11. M181 DENOTES PART W/O POLARIZING KEY



RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES [MM]


TOLERANCES:

ANGULAR: $\pm 1^\circ$

DECIMALS
XX = $\pm .012 [.3]$
.XXX = $\pm .008 [.20]$
.XXXX = $\pm .0040 [.100]$

DRAWN DATE NAME
10/28/08 JH

THE INFORMATION HEREIN CONTAINS
PROPRIETARY INFORMATION OF
SULLINS ELECTRONICS AND IS NOT
TO BE REPRODUCED, USED OR
DISCLOSED TO OTHERS FOR ANY
PURPOSE EXCEPT AS SPECIFICALLY
AUTHORIZED IN WRITING BY AN
OFFICER OF SULLINS ELECTRONICS.



TITLE
HEADER FEMALE, .079[2.00] CC, SR w/o POLARIZING KEY

PART NUMBER
SFH213-PP_N-D_ _-ID- _-M181

SIZE CAGE CODE DWG. NO. REV
C 54453 11157 E

SCALE: 4:1 SHEET 1 OF 1