



Select a Category

GO

## 60000 SERIES INSULATED BELL-MOUTH TERMINALS

[Product Index](#) > [Terminals & Cable Ties](#) > [Terminals](#) > [60000 Series Insulated Bell-Mouth Terminals](#) > C61438

**60000 Series Insulated Bell-Mouth - Ring Tongue, 25/64" Hole, 12-10 AWG**

- Flared, vinyl insulated sleeve to allow easier insertion of the wire, or wires with extra heavy-duty insulation.
- Insulation is color-coded to indicate wire size, yellow for 12-10 gauge.
- 100 pieces per reusable C-Pack.



**Buy Now!**

Pictured: C61314

Cat. No.	Hole Dia.	Length	Sleeve Color	Stud Size	Weight Per (oz.)	Width	Wire Size
C61438	25/64"	1-13/32"	yellow	3/8	.0823	19/32"	12-10

All dimensions are in inches and (millimeters) except where indicated.

[Download High-Resolution .jpg photo](#)

[Download High-Resolution .eps photo](#)



The downloadable files are compressed in .zip format to save on downloading times.  
Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.

---

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).