

Part # 9312, 16 AWG Stranded Tinned Copper Wire Mil-W-16878/1 Type "B", Consolidated Hook-Up Wire



16 AWG Stranded Tinned Copper Wire Mil-W-16878/1 Type "B", Consolidated Hook-Up Wire

- Product Construction**
- Conductor:**
- 16 AWG Annealed Stranded Tinned Copper Wire Conductor per ASTM B-33
- Insulation:**
- Mil-W-16878/1, Type "B" color coded PVC Insulation
Temperature -50°C to +105°C
- Voltage Rating:**
- Mil-W-16878/1, Type "B" 600 volts
- Applications:**
- Hook Up wire
 - Pont to point wiring
 - Internal wiring of meters, panels, electrical and electronic equipment
- Packaging:**
- 1000 ft. spools
 - 100 ft. spools
 - Also available on bulk reels

SPECIFICATIONS

MIL Type	Type "B" MIL-W-16878/1
Gauge	16 AWG
Strands	19 x 29 Tin Copper Wire
Nominal Insulation Wall	0.010 in.
Insulation Type	PVC
Nominal O.D.	0.077 in.
Color	0-Black/1-Brown/2-Red/3-Orange/4-Yellow/5-Green/6-Blue/7-Violet/8-Gray/9-White
Color Code Chart	Chart-Hook-Up Wire
Insulation Temperature	-50 to +105 °C
Voltage	600 V