




| DATE | SYM | REVISION RECORD | AUTH | DR. | CK. |
|------|-----|-----------------|------|-----|-----|
|      |     |                 |      |     |     |
|      |     |                 |      |     |     |
|      |     |                 |      |     |     |



## SPECIFICATIONS :

Plastic material - polypropylene  
 Flammability rating-UL94 HB, UL file no. E216959  
 Temperature Range: -10°C to +100°C  
 Springs - nickel plated spring steel  
 Bump plates - Brass, nickel plated  
 Contact Resistance: Under 50mΩ for +/- contacts per EIA-540J000  
 ROHS COMPLIANT

**Note:** Dimensions in mm. ( inches )

|                                 |                                       |                                                                                                                                                                                    |             |
|---------------------------------|---------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| TOLERANCES<br>(EXCEPT AS NOTED) |                                       |  <b>Memory Protection Devices, Inc.</b><br>200 Broad Hollow Road, Farmingdale, New York 11735 |             |
| DECIMAL                         |                                       | SCALE                                                                                                                                                                              | DRAWN BY    |
| + .5 (.020")                    |                                       | NONE                                                                                                                                                                               | B.S.        |
|                                 |                                       |                                                                                                                                                                                    | APPROVED BY |
| FRACTIONAL                      | TITLE                                 |                                                                                                                                                                                    |             |
| + .8 (.030")                    | SIX "AA" CELL HOLDER WITH BUMP PLATES |                                                                                                                                                                                    |             |
| ANGULAR                         | DATE                                  | DRAWING NUMBER                                                                                                                                                                     |             |
| + 3°                            | 08/19/2011                            | BH26AAB                                                                                                                                                                            |             |