

Sales Outline Drawing

Revision

A

OBSOLETE- USE PK-27N25WQ

Specifications

Resonant Frequency (Hz)	2500 $\pm$ 500
Operating Voltage (Vdc)	3 ~ 28
Rated Voltage (Vdc)	12
Current Consumption Max. (mA)	8 at Rated Voltage
Sound Pressure Level Min. (dB)	90 at 30cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 707 UL94HB plastic resin (Color: Black)
Leading Wire	28 AWG
Weight (Grams)	6.6
Options	For other options contact factory

Dimensions: (units: mm)

