

208 RS series



features



- Direct replacement for T6.8 Slide Base
- Flat topped for enhanced, even illumination of large lens areas
- Water clear lens
- Durable to shock and vibration
- Ideal for industrial pushbutton switches and annunciator panels
- Pack Quantity = 20 Pieces

specifications

Ordering information and typical characteristics (Ta = 25°C)

RS Part Number	Marl Part Number	Colour	Voltage Vac/dc	Current DC (mA)	Luminous Intensity (mcd)	Wave Length (nm)	Operating Temp. (°C)	Storage Temp. (°C)	De-rating Graphs
2387905	208-501-21-38	Red	12 Vdc	10	600	630	-40 - +80	-40 - +100	D
2387961	208-501-22-38	Red	24 Vdc	17	600	630	-40 - +80	-40 - +100	D
2387983	208-521-22-38	Yellow	24 Vdc	19	600	585	-40 - +80	-40 - +100	D
2387911	208-532-21-38	Green	12 Vdc	20	800	515	-40 - +80	-40 - +100	F
2387977	208-532-22-38	Green	24 Vdc	20	800	515	-40 - +80	-40 - +100	F
2830049	208-997-22-38	White	24 Vdc	20	1100	* See pg.2	-30 - +85	-40 - +100	I
2830055	208-997-23-38	White	24-28 Vdc	20	1100	* See pg.2	-30 - +85	-40 - +100	I

^ = Voltage for 20mA product is Vf at 20mA, not Vopr

- Products must be de-rated according to the de-rating information. Each de-rating graph refers to specific LEDs. Please refer to graphs on page 2.

- Luminous intensity is measured at 20mA on a discrete LED unless otherwise stated.


© marl international limited technical documentation has been designed by marl international limited for the intention of providing information, which must not be copied or released to a third party without prior written consent from marl international limited. the information provided does not constitute part of any order or contract and should not be regarded as a representation relating to either products or service. no responsibility can be assumed for inaccuracies or printing errors. marl international limited reserve the right to alter without notice the specification or any conditions of supply for product or service.



208 RS series



technical data



+ Printed on base denotes Anode. Colour dot on product denotes LED colour.




Dimensions in mm (typical)
Not to scale

Lamp Base Style	Series	Metric Equivalent (mm)	Max. Power Dissipation (mW)
T6.8 Slide Base	208	-	625

997F-C	*Typical emission colour White			
x	0.31	-	-	-
y	0.32	-	-	-

Intensities (lv) and colour shades of white (x,y co-ordinates) may vary between leds within a batch

de-rating information



© marl international limited technical documentation has been designed by marl international limited for the intention of providing information, which must not be copied or released to a third party without prior written consent from marl international limited. the information provided does not constitute part of any order or contract and should not be regarded as a representation relating to either products or service. no responsibility can be assumed for inaccuracies or printing errors. marl international limited reserve the right to alter without notice the specification or any conditions of supply for product or service.



208 RS series



also available

Part numbers also available in the 208 series:

Part Number	Colour	Voltage Vopr
208-501-22	Red	24 Vdc
208-501-23-38	Red	28 Vdc
208-501-24-38	Red	48 Vdc
208-501-48	Red	60 Vdc
208-514-22	Green	24 Vdc
208-521-04-38	Yellow	20 mA dc
208-521-21-38	Yellow	12 Vdc
208-521-22	Yellow	24 Vdc
208-521-23	Yellow	28 Vdc
208-521-23-38	Yellow	28 Vdc
208-521-42	Yellow	15 Vdc
208-532-22	Green	24 Vdc
208-532-23-38	Green	28 Vdc
208-532-24	Green	48 Vdc
208-930-21-38	Blue	12 Vdc
208-930-22-38	Blue	24 Vdc
208-930-23-38	Blue	28 Vdc
208-993-21-38	Warm White	12 Vdc
208-993-22-38	Warm White	24 Vdc
208-993-23-38	Warm White	28 Vdc
208-993-24-38	Warm White	48 Vdc
208-993-42-38	Warm White	15 Vdc
208-993-48-38	Warm White	60 Vdc
208-993-50-38	Warm White	125 Vdc
208-997-21-38	White	12 Vdc
208-997-24-38	White	48 Vdc
208-997-26-38	White	230 Vdc
208-997-48	White	60 Vdc
208-997-48-38	White	60 Vdc
208-997-75-38	White	110 Vac 50 Hz
208-997-80-38	White	60 Vac 50 Hz

RP = Reverse Polarity

© marl international limited technical documentation has been designed by marl international limited for the intention of providing information, which must not be copied or released to a third party without prior written consent from marl international limited. the information provided does not constitute part of any order or contract and should not be regarded as a representation relating to either products or service. no responsibility can be assumed for inaccuracies or printing errors. marl international limited reserve the right to alter without notice the specification or any conditions of supply for product or service.



208 RS series



design considerations

Single-Chip LEDs

All devices feature water clear high intensity LEDs as standard. In devices where discrete LEDs are used, the single chip LED devices have been modified by the removal of the domed portion of the encapsulation (flat-topped) to provide even illumination of switches and annunciators. Non flat topped versions are also available.

Flat-topping does not apply to devices using surface-mounted device (SMD) LEDs.

Product Evaluation

Filament replacement LEDs have been specifically designed to meet the primary objective of providing improved reliability. As this product range is suitable for both new-build and retro-fit, (sometimes in very old systems), a wide range of illuminated push button switches and lamp holders can be encountered. Due to subjectivity, evaluation of the LED type is recommended, (samples of all standard models are available). Care should be taken to correctly simulate operating ambient light conditions to ensure that the correct device has been selected to maximise viewing characteristics such as viewing angle, colour compatibility and on/ off contrast ratio.

Electro-Static Discharge (ESD)

Build up of electro-static discharge occurs in many situations involving people moving and handling products. The range of possible situations is very diverse but voltage levels as high as several thousand volts can and do arise in many individual situations. When an operator charged up to these levels handles a static sensitive device, there is a very probable likelihood that the device will be irreversibly damaged. It is essential that precautions are taken at all stages during manufacture and assembly of these products. Although LEDs were never considered to be static sensitive devices, changes in manufacturing technology and materials used to produce higher intensity products over a large range of the wavelength spectrum have changed this. Marl has an approved system of ESD control from goods in, through production and into final packing and despatch. Marl recommend all users of LED based products follow the guidelines of BS 100015.

Power De-Rating

The forward voltage/ current value of an LED is dependant upon the ambient temperature of the environment in which it is operated. Therefore, care must be taken to operate the LED at the correct voltage/ current values, depending upon the ambient temperature. Consequently, a recommendation regarding operating voltages and currents is given in order to address these temperature effects. This recommendation is termed 'de-rating'. It is usual for forward voltages and currents to be specified for ambient temperature of 25°C. However, because the values of these qualities vary with temperature, marl should be contacted if the device is to be operated at a temperature significantly higher than 25°C. Marl accept no liability for any product that is operated higher than the stated voltage.

© marl international limited technical documentation has been designed by marl international limited for the intention of providing information, which must not be copied or released to a third party without prior written consent from marl international limited. the information provided does not constitute part of any order or contract and should not be regarded as a representation relating to either products or service. no responsibility can be assumed for inaccuracies or printing errors. marl international limited reserve the right to alter without notice the specification or any conditions of supply for product or service.

