







LOC	DIST	REVSIONS 変更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J			P	REVISED PER ECO-11-005140	02APR2011	RK	HMR
			PI	REVISED ECR-11-007131	14JUN11	RK	HY
			R	REVISED ECR-15-013494	18SEP2015	KK	RK



B - B



C - C

1. 適用電線：
AVSS, AVSSH-f 0.3-0.5mm²
CAVS, CAVUS 0.22-0.5mm²
2. 取付適用規格： 114-5250
3. アプリケータ送りピッチ： 7.5mm
4. パラ端子型番：
PRE-TIN; 1318143-1
SELECTIVE GOLD; 1318143-2

△5 識別用金めっき範囲を示す。

△ 識別用刻印

1. APPLICABLE WIRE RANGE ;
AVSS,AVSSH-f 0.3-0.5mm²
CAVS,CAVUS 0.22-0.5mm²
2. APPLICATION SPEC ; I14-5250
3. APPLICATOR FEED; 7.5mm.
4. P/N OF LOOSE PIECE;
PRE-TIN; I318143-1
SELECTIVE GOLD; I318143-2

△ 5 GOLD PLATED AREA FOR DISCRIMINATION.

△6 MARKING FOR IDENTIFICATION.

	SEE DRAWING 1123343-7	1123343-7
OBSOLETE	—//—	1123343-5
	 SELECTIVE GOLD	1123343-2
	PRE-TIN	1123343-1
	FINISH	PART NO.


WIRE RANGE 絕合電線斷面積	0.22-0.56mm ²	INSULATION DIA 被覆外徑	Ø0.95-1.7
-----------------------	--------------------------	------------------------	-----------

 TE Connectivity	
NAME 名称	025 RECEPTACLE CONTACT 025 RECEPTACLE CONTACT

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A2	00779	005 C-1123343	
----	-------	------------------	---

SCALE	0 :	SHEET	1	OF	1	REV	R
-------	-----	-------	---	----	---	-----	---

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWNN H. YAMAGAMI CHK T. KOHNO APVD N. SAI	25JAN99 25JAN99 25JAN99
DIMENSIONS: 単位: 概 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差: ± 0.2	
		4 P L C ± 0.1 2 P L C ± 0.15 3 P L C ± 0.001 4 P L C ± 0.0001	PRODUCT SPEC 製品規格 - APPLICATION SPEC 取付適用規格 114-5250
		ANGLES 仕上 $\pm 3^{\circ}00'$	
		WEIGHT 0.2g	
		MATERIAL 材料 COPPER ALLOY	
		SEE TABLE	
		Customer Drawing	