




Rotary Switches

10YD025, 10YD026,
10YD034, 10YD043,
10YD062, 10YD112

Dimensions: mm (in)



Electrical Specifications:

- Rating: 0.3A 125VAC
- Contact resistance: 30mΩ max. @ 1A
- Insulation resistance: 10MΩ @ 500VDC min.
- Dielectric strength: 500VAC for 1 minute

Mechanical Specifications:

- Type: non-shorting contact (break before make)
- Rotation torque: 1~3KG/cm

Materials:

- Hardware included: 1 hexagon nut & 2 washers
- Shaft: 1/4"

Mouser Stock No.	Poles	Position
10YD025	2	5
10YD026	2	6
10YD034	3	4
10YD043	4	3
10YD062	6	2
10YD112	1	12

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha \(Taiwan\):](#)

[SR2511-0403-19F0B-E9-N-W](#)