

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200790226

Status:

Active

Overview:

Brad Ultra-Lock Connection System

Description:

Ultra-Lock (M12) Single-Ended Cordset, 3 Poles, Male (90°) to Pigtail, 22 AWG, TPE Cable, 2.0m (6.56') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

General

Product Family

Series

Connector End A

Connector End B

IP Rating

Material - Contact

Overview

Product Name

Protocol

Region

Type

UPC

Industrial Cordsets

120079

Ultra-Lock (M12)

Pigtail

IP69K

Copper Alloy

Brad Ultra-Lock Connection System

Ultra-Lock (M12)

EtherNet

America

Single Ended

78678884215

Physical

Cable Diameter

Cable Length

Color - Cable Jacket

Coupling Style

Gender

Keyway

LED Indicator

Material - Cable Jacket

Material - Connector Body

Material - Coupling Nut

Material - O-Ring

Material - Plating Mating

Orientation

Poles

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

N/A

2.0m (6.56')

Yellow

Push to Lock

Male-Pigtail

Single

No

TPE

TPE

Nickel-plated Brass

Fluoro-elastomer

Gold

90° to Pigtail

3

-25°C to +90°C

22

PLTC-ER

Electrical

Current - Maximum per Contact

Voltage - Maximum

4.0A

250V AC/DC

Material Info

Engineering Number

W03007K05M020

Reference - Drawing Numbers

Sales Drawing

SD-120079-032



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

120079 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION