




Model #:	Ø Dimension "A"	Ø Dimension "B"	Accepts Wire AWG:
4933	.062" (1,57mm)	.160" (4,06mm)	18, 20, 22
4986	.120" (3,05mm)	.200" (5,08mm)	14, 16

FEATURES:

- Threaded two piece design allows wires to be soldered or crimped to the banana plug.
- Heavy-duty plastic body withstands cracking if accidentally dropped.
- Banana plug spring is nickel plated Beryllium Copper for long insertion life.
- Fits into Pomona Models 4921, 4934, and 4987 Sheathed Banana Jacks.

MATERIALS:

Banana Plug: Body – Brass, Nickel Plated

Spring – Beryllium Copper, Nickel Plated

Insulation: Nylon, Color per part number

Threaded Handle: Nylon, Color per part number, Marking: "POMONA ELECT. 4933 or 4986"

RATINGS:

Operating Voltage: 1200 Volts AC/DC

Current: 15 Amperes Max.

Operating Temperature: +80°C (+176°F)

ORDERING INFORMATION: Model 4933-* or 4986-*

* = Color, Standard Colors: -0 Black, -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA