

- Replacement for incandescent 40 W
- Up to 85% energy saving
- Lifetime of 30,000 hrs
- An energy efficient LED solution for general lighting.  
It is the ideal light source for all fields of application of 40 W lamps.



Order Code 52113

#### General Data

|             |         |
|-------------|---------|
| Lamp Socket | B22     |
| Design      | Frosted |

#### Geometric Data

|               |     |
|---------------|-----|
| Length (mm)   | 110 |
| Diameter (mm) | 60  |
| Weight (g)    | 155 |

#### Electric Data


|                          |         |
|--------------------------|---------|
| Wattage (W)              | 7.3     |
| Voltage (V)              | 220-240 |
| Power Factor             | ≥ 0.90  |
| Operating Frequency (Hz) | 50-60   |

#### Photometric Data

|                         |                   |
|-------------------------|-------------------|
| Luminous Flux (lm)      | 480               |
| CRI                     | ≥ 80              |
| CCT (K)                 | 3000 – warm white |
| Luminous Intensity (cd) | -                 |
| Beam Angle (°)          | -                 |
| Lifetime (hrs)          | 30,000            |

|                 |        |
|-----------------|--------|
| Switching cycle | 20,000 |
|-----------------|--------|

|                        |    |
|------------------------|----|
| Wattage Equivalent (W) | 40 |
|------------------------|----|





**Order Code** 52113

**Product Description** LED CLASSIC A B22 7.3W 3000K WW 480LM Blister

## Technical Packaging Details

|                            |                                 |
|----------------------------|---------------------------------|
| Barcode                    | 023942521136                    |
| EAN 128                    | (02)00023942521136(37)04(91)204 |
| EAN 14                     | 50023942521131                  |
| Pack Dimensions (HxWxL)    | 198 mm x 118 mm x 61 mm         |
| Pack Weight                | 180 g                           |
| Carton Qty (Shipping Unit) | 4                               |
| Carton Dimensions (HxWxL)  | 208 mm x 135 mm x 248 mm        |
| Cartons/Pallet             | 96                              |
| Layers/Pallet              | 4                               |
| Units/Pallet               | 384                             |

## Photometric Diagram

52113

