

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39543-5119](#)
Status: **Active**
Overview: Eurostyle™ Terminal Blocks
Description: 5.00mm Pitch Eurostyle™ Horizontal Fixed Mount PCB Terminal Block, with Standard Imprinting, 19 Circuits

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General

Product Family Terminal Blocks
Series [39543](#)
Application N/A
Comments with Standard Imprinting
Component Type One Piece
Overview [Eurostyle™ Terminal Blocks](#)
Product Name ESE, Eurostyle™Fixed Mount
Type Euro Block
UPC 822350544917

Physical

Circuits (Loaded) 19
Entry Angle Vertical
Lock to Mating Part None
Number of Rows 1
Orientation Horizontal
PC Tail Length 3.50mm
PCB Thickness - Recommended 2.50mm
Panel Mount No
Pitch - Mating Interface 5.00mm
Pitch - Termination Interface 5.00mm
Polarized to Mating Part N/A
Stackable No
Temperature Range - Operating -40°C to +105°C
Wire Size AWG 16, 18, 20, 22, 24
Wire Size mm² 0.20 - 1.31

Electrical

Current - Maximum per Contact 10A
Voltage - Maximum 300V

Solder Process Data

Duration at Max. Process Temperature (seconds) 5
Lead-free Process Capability Wave Capable (TH only)
Max. Cycles at Max. Process Temperature 135
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Sales Drawing SD-39543-006



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[39543Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

39543-5119