

▶IPRO-LITE

Product Data Specification

PRO-LITE - 20 LED GU10 PAR16 240V

DESCRIPTION


The LED GU10 is a like for like size replacement for the 240V GU10 lamp. Available in a wide range of colours including a colour changing model, the lamps have an ultra long life of 30,000 hours.

APPLICATIONS

- Domestic & Commercial
- Areas of difficult access

FEATURES


- 30,000 hr average lamp life
- Low maintenance
- 240V input with GU10 cap
- Very low heat output
- Clear lens
- Ease of installation
- RoHS compliant




= 10




= 200




= 14



= 66



= 5 x 5 x 6 cm



= 56 x 29 x 28 cm

TECHNICAL SPECIFICATION

Product Code	Wattage	Colour	Number of LEDs	LED Angle
GU10/LED/BLUE	1.8	Blue	20	15
GU10/LED/GREEN	1.8	Green	20	15
GU10/LED/MAGENTA	1.8	Magenta	20	15
GU10/LED/ORANGE	1.8	Orange	20	15
GU10/LED/RED	1.8	Red	20	15
GU10/LED/CHANGER	1.8	RGB Colour Changer	18	15
GU10/LED/UV	1.8	Ultra Violet	20	15
GU10/LED/WHITE	1.8	White	20	15