

Plug 'n' Play compact axial fans

Complete with mountings and connector



- DC fans
- Plastic housing
- Ideal for PC cooling
- Molex connector fitted
- Threaded inserts for easy mounting
- Connection via lead 313mm (+/- 10mm)
- Threaded brass inserts fitted on both sides
- Blowing over struts
- Protection IP20

	Airflow	Airflow	Voltage	Voltage Range	Noise	Sound Power	Bearings	Power	Speed	Temp range	Length	Width	Depth	Insert thread size	Connector
Part Number	m³/h	CFM	VDC	VDC	dB(A)	Bel		W	RPM	°C	mm	mm	mm		
412-F00	10	5.9	12	10-14	18	3.8	Sleeve	0.9	6000	-20...+70	40	40	20	M3	Molex 22-01-2025
414F-F00	8	4.7	24	20-28	22.1	4.4	Sleeve	0.8	5400	-20...+70	40	40	10	M3	Molex 22-01-2025
414-F00	10	5.9	24	20-28	18	3.8	Sleeve	1	6000	-20...+70	40	40	20	M3	Molex 22-01-2025
612F-F00	29	17.1	12	10.8-13.2	27	4.4	Sleeve	1	3900	-20...+70	60	60	15	M3	Molex 22-01-2025
612NGN-F00	41	24.1	12	8-15	35	5.2	Sleeve	2.1	5100	-20...+70	60	60	25	M3	Molex 22-01-2025
612NGH-F00	46	27.1	12	18-15	38	5.5	Sleeve	2.6	5600	-20...+70	60	60	25	M3	Molex 22-01-2025
614F-F00	29	17.1	24	21.6-26.4	27	4.4	Sleeve	1.1	3900	-20...+70	60	60	15	M3	Molex 22-01-2025
614NGHH-F00	56	33	24	18-28	43	6.3	Sleeve	3.8	6850	-20...+70	60	60	25	M3	Molex 22-01-2025
8414NGL-F00	33	19.4	24	18-28	12	3.5	Sleeve	0.7	1500	-20...+70	80	80	25	M3	Molex 22-01-2025
8414NGH-F00	79	46.5	24	18-26	37	5	Sleeve	2.8	3600	-20...+70	80	80	25	M3	Molex 22-01-2025

Fixing Centres

Frame Size	Dimension A (mm)
40	32
60	50
80	71.5

