






FCIconnect.com


Copyright FCI

PRODUCT NUMBER
SEE NOTE 1



mat'l. code NOTE 3				surface ISO 1302	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecn	no	dr	date	tolerances unless otherwise specified	scale 1:1	title
A	V12494	SAR		9/09/91	angles		3 ROW VERTICAL RECEPT.
B	V31616	SRS		10/26/93	linear		HIGH DURABILITY, S.T.B., 0 G.P.
C	V40678	GIP		3/29/94	σ±2'		dwg no
D	V90521	HTB	2/25/99	dr	S. ROYER	8/16/91	sheet 1 of 2 size
E	V00258	JWS	1/21/00	enr	S. CLARK	8/16/91	50022 A3
F	M06-0255	MNR	7/06/06	chr	S. CLARK	8/16/91	type
				appd	S. CLARK	8/16/91	Product Customer Drawing
sheet index	revision	F	F				
	sheet	1	2				

form: A3



- NOTES:
- ① PRODUCT NUMBERING CODE:
50022 - X YYY Z
TAIL LENGTH(NOTE 5)
NO. OF POSITIONS(NOTE 2)
PLATING(NOTE 4)
BASE NUMBER
 - ② THIS PRODUCT IS CONFIGURED IN SIZES OF 10 THRU 80 COLUMNS IN INCREMENTS OF ONE. i.e.: 10,11,12,13,.....79,80.
 - ③ HOUSING MATERIAL: GLASS AND MINERAL FILLED HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER UL94V-0. COLOR: BLACK.
CONTACT MATERIAL: BeCu
 - ④ PLATING CONTACT AREA OPTIONS:
7 = 60u"/1.52u GXT
ALL SOLDER TAILS TIN/LEAD.
 - ⑤ TAIL LENGTH OPTIONS:
E = .125±.010 / 3.18±.25
F = .145±.010 / 3.68±.25
H = .180±.010 / 4.57±.25
 - ⑥ MANUFACTURE'S NAME, P/N AND LOT CODE TO APPEAR ON THIS SURFACE AS PER BUS-12-108.
 - ⑦ FOR DOCUMENTATION MENU, SEE BUS-01-057.

mat'l. code				surface ISO 1302 ✓ ISO 406 ISO 1101		tolerance ISO 1101		projection 		product family HPC				
ltr	ecn	no	dr	date		tolerances unless otherwise specified				title				
F						angles	linear	.XX ±.01/.3 .XXX ±.005/.13 0'±2' .XXXX ±.0020/.051	INCH/MM 	3 ROW VERTICAL RECEPT. HIGH DURABILITY, S.T.B., 0 G.P.				
						dr	S. ROYER	8/16/91		dwg no		sheet2 of 2		size
						enrg	S. CLARK	8/16/91		50022		A3		
						chr	S. CLARK	8/16/91						
						appd	S. CLARK	8/16/91		type		Product Customer Drawing		
sheet index		revision sheet												