



AMPROBE®

AMB-25 & AMB-35

Digital Megohmmeters - Insulation Resistance Testers



Quality does not have to be expensive. These affordable megohmmeters still offer a solid range of features designed to meet most insulation test applications.

- Test insulation of wires, cables, transformers and motors
- Come as a complete kit including test leads
- Selectable test voltages up to 1000V
- Button Lock for Dielectric Absorption Ratio Test
- Sensitive Ohmmeter for checking resistance of motor windings
- Built in voltmeter (AMB-35 only)
- Internal memory (stores 9 readings)
- Fast and easy to use, rugged durable design



FEATURES	AMB-25	AMB-35	ACCURACY
Insulation resistance with 250, 500 & 1000 VDC test voltages	0 - 4.000 / 40.00 / 400.0 / 4000 M Ω	0 - 4.000 / 40.00 / 400.0 / 4000 M Ω	$\pm 3\%$ Rdg ± 5 LSD < 1G Ω $\pm 5\%$ Rdg ± 5 LSD < 4G Ω
Resistance	0 - 9999 Ω	0 - 9999 Ω	1% Rdg ± 2 LSD
Low Resistance		0.10 - 40.00 Ω	2% Rdg ± 2 LSD
AC/DC Voltage		0.1 - 1000.0V	$\pm 2.0\%$ Rdg ± 1 LSD

REPLACEMENT PARTS (supplied with product)	PART NUMBER
Test leads complete set	MTL-45
Instruction Manual	www.AMPROBE.com

OPTIONAL ACCESSORIES	PART NUMBER
Carrying case	GP-2CC



Miramar, FL 33025 • Toll Free: 800-327-5060 • Phone: 954-499-5400 • Fax: 954-499-5418 • www.Amprobe.com

www.AMPROBE.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMPROBE:](#)

[AMB-25](#)