






TO SNAP-LOCK IN A .100±.002 [2.54±0.05] DIA. HOLE,
IN A .064 [1.63] MAX THICK BOARD

NOTES:
1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01).
FLAME RETARDANT NYLON 6/6 UL 94 V-0 (RMS-19),
AVAILABLE BY SPECIAL ORDER ONLY.
2. COLOR: NATURAL.

PART NO.	DIM. "A"±.015
PST-1-01	1/16 [1.6]
PST-2-01	1/8 [3.2]
PST-3-01	3/16 [4.8]
PST-4-01	1/4 [6.4]
PST-5-01	5/16 [7.9]
PST-6-01	3/8 [9.5]
PST-7-01	7/16 [11.1]
PST-8-01	1/2 [12.7]
PST-9-01	9/16 [14.3]
PST-10-01	5/8 [15.9]

1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01). FLAME RETARDANT NYLON 6/6 UL 94 V-0 (RMS-19), AVAILABLE BY SPECIAL ORDER ONLY.			TITLE: PUSH SPACER, TEARDROP					 		DWG IN IN [MM]							
2. COLOR: NATURAL.			CREATED USING SOLIDWORKS		FILE #: PST			DWN: SK		APP: RT		FINAL					
			TOLERANCES UNLESS NOTED		SHEET: 1 OF 1		SHEET SIZE: A		DT: 09/27/05		CHKD: RT		PART #		PRINT TYPE		
					RE: RICHCO, INC.		RICHCO, INC.		ENG@RICHCO-INC.COM		(773) 539-4060		SEE TABLE		CA		
					.XX=±.010												
					.XXX=±.005												
					FRAC.=±1/64												
					ANG.=±1°												
B			REDRAWN FROM ACAD TO SOLIDWORKS, SEE ECN#1062			SK		09/28/05									
A			CHANGED FILE NO. AND TITLE BLOCK			SM		05/04/01									
REV.			DESCRIPTION			ENGR.		DATE									